

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
100.0	0.01	48.5	51.5
200.0	0.01	42.8	45.5
300.0	0.02	40.8	42.4
400.0	0.02	40.2	40.8
500.0	0.03	40.3	39.8
600.0	0.03	40.8	39.3
700.0	0.04	41.8	39.7
800.0	0.04	42.9	41.2
900.0	0.04	44.1	42.9
1000.0	0.02	43.8	44.8
1100.0	0.01	42.2	43.0
1500.0	0.03	35.3	33.9
1750.0	0.05	38.9	37.4
2000.0	0.06	33.4	31.6
2500.0	0.07	36.3	34.1
3000.0	0.07	33.5	35.0
3500.0	0.07	32.5	35.9
3750.0	0.07	31.7	34.3
4000.0	0.07	33.3	34.7
4500.0	0.07	33.0	35.0
4750.0	0.06	34.7	34.3
5000.0	0.06	34.9	35.5
5500.0	0.06	37.2	35.9
6000.0	0.05	34.4	35.7
6500.0	0.05	39.7	39.2
7000.0	0.06	34.6	36.1
7500.0	0.04	33.7	34.4
8000.0	0.02	31.9	32.3
8500.0	0.02	30.6	31.0
9000.0	0.01	28.7	29.9
9500.0	0.10	26.0	26.5
10000.0	0.15	23.5	23.4
10500.0	0.11	22.3	22.9
11000.0	0.16	23.1	24.3
11500.0	0.20	23.6	24.9
12000.0	0.18	22.1	23.0
12500.0	0.19	23.7	24.0
13000.0	0.19	25.8	24.2
13500.0	0.07	23.9	21.6
14000.0	0.15	22.3	20.9
14500.0	0.21	23.5	22.4
15000.0	0.25	23.0	22.3
15500.0	0.29	22.1	21.4
16000.0	0.23	23.7	22.4
16500.0	0.14	25.7	24.5
17000.0	0.21	25.1	24.2
17500.0	0.27	26.0	25.3
18000.0	0.28	25.1	24.6