

Non-Magnetic Flex Cable SMA Male to SMA Male

141N-50CSM

Typical Performance Data

FREQ.	INSERTION LOSS	SMA MALE RETURN LOSS IN	SMA MALE RETURN LOSS OUT
(GHz)	(dB)	(dB)	(dB)
0	0.02	57.65	56.24
1	0.18	45.07	45.17
2	0.26	43.81	43.45
3	0.33	44.51	45.62
4	0.39	46.73	47.13
5	0.45	35.12	35.30
6	0.50	32.87	32.80
7	0.55	37.27	37.84
8	0.60	39.05	38.89
9	0.65	38.22	37.73
10	0.69	34.73	34.24
11	0.74	34.17	34.24
12	0.78	30.75	30.48
13	0.82	27.74	27.63
14	0.86	32.76	33.58
15	0.90	33.19	33.91
16	0.94	30.34	30.14
17	0.98	24.59	24.33
18	1.02	22.95	22.93



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
 141N-50CSM
 3/25/2026
 Page 1 of 1