

4 Way-0° Power Splitter/Combiner

BP4C+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
560.0	9.19	9.60	9.59	9.39	0.41	4.78	15.22	14.51	16.06	3.76	1.42	1.51	1.51	1.50
567.5	9.02	9.43	9.41	9.21	0.40	4.53	15.45	14.74	16.33	3.59	1.41	1.51	1.50	1.50
575.0	8.86	9.26	9.25	9.05	0.40	4.31	15.68	14.97	16.60	3.43	1.41	1.51	1.50	1.49
582.5	8.71	9.10	9.09	8.89	0.39	4.05	15.93	15.22	16.89	3.27	1.40	1.50	1.50	1.48
590.0	8.56	8.95	8.93	8.74	0.39	3.83	16.18	15.47	17.19	3.13	1.40	1.50	1.50	1.48
597.5	8.42	8.80	8.78	8.60	0.38	3.58	16.44	15.74	17.51	2.99	1.39	1.50	1.50	1.47
605.0	8.28	8.66	8.64	8.46	0.38	3.36	16.71	16.01	17.83	2.86	1.39	1.50	1.49	1.47
612.5	8.15	8.52	8.51	8.33	0.37	3.14	16.98	16.30	18.18	2.74	1.38	1.49	1.49	1.46
620.0	8.03	8.40	8.38	8.20	0.36	2.91	17.26	16.59	18.53	2.62	1.37	1.49	1.49	1.45
627.5	7.92	8.28	8.26	8.08	0.36	2.70	17.55	16.89	18.89	2.51	1.37	1.49	1.49	1.45
635.0	7.81	8.16	8.15	7.97	0.36	2.48	17.84	17.20	19.27	2.41	1.36	1.48	1.48	1.44
642.5	7.70	8.05	8.04	7.86	0.35	2.26	18.15	17.52	19.67	2.31	1.36	1.48	1.48	1.43
650.0	7.61	7.95	7.93	7.76	0.34	2.05	18.45	17.85	20.08	2.22	1.35	1.47	1.47	1.42
657.5	7.51	7.85	7.84	7.67	0.34	1.84	18.76	18.18	20.50	2.13	1.35	1.47	1.47	1.42
665.0	7.43	7.76	7.74	7.58	0.33	1.62	19.07	18.53	20.93	2.05	1.34	1.47	1.47	1.41
672.5	7.35	7.67	7.66	7.49	0.33	1.46	19.38	18.88	21.38	1.97	1.33	1.46	1.46	1.40
680.0	7.27	7.59	7.58	7.42	0.33	1.37	19.69	19.24	21.84	1.90	1.33	1.46	1.46	1.40
687.5	7.20	7.52	7.50	7.34	0.32	1.25	20.00	19.60	22.30	1.83	1.32	1.45	1.45	1.39
695.0	7.13	7.44	7.43	7.27	0.31	1.15	20.30	19.96	22.77	1.77	1.32	1.44	1.45	1.38
702.5	7.07	7.38	7.36	7.21	0.31	1.03	20.59	20.33	23.25	1.71	1.31	1.44	1.44	1.37
710.0	7.01	7.31	7.30	7.15	0.30	0.94	20.88	20.69	23.72	1.65	1.31	1.44	1.44	1.37
717.5	6.96	7.26	7.24	7.09	0.30	0.84	21.16	21.05	24.19	1.59	1.30	1.43	1.43	1.36
725.0	6.91	7.20	7.19	7.04	0.29	0.73	21.41	21.41	24.64	1.54	1.29	1.42	1.43	1.35
732.5	6.87	7.15	7.14	7.00	0.29	0.79	21.65	21.77	25.06	1.49	1.29	1.42	1.42	1.35
740.0	6.83	7.11	7.09	6.95	0.28	0.87	21.87	22.11	25.45	1.45	1.28	1.41	1.42	1.34
747.5	6.79	7.07	7.05	6.91	0.28	0.97	22.06	22.43	25.78	1.40	1.28	1.41	1.41	1.33
755.0	6.75	7.03	7.01	6.88	0.27	1.03	22.23	22.73	26.10	1.36	1.27	1.40	1.41	1.33
762.5	6.72	6.99	6.97	6.84	0.27	1.12	22.38	22.98	26.34	1.32	1.27	1.40	1.40	1.32
770.0	6.69	6.96	6.94	6.81	0.26	1.22	22.50	23.21	26.52	1.29	1.26	1.39	1.40	1.32
777.5	6.67	6.93	6.91	6.78	0.26	1.27	22.59	23.40	26.59	1.25	1.26	1.39	1.39	1.31
785.0	6.65	6.90	6.88	6.76	0.25	1.44	22.63	23.58	26.61	1.22	1.25	1.38	1.39	1.31
792.5	6.63	6.87	6.85	6.73	0.25	1.62	22.66	23.71	26.53	1.19	1.25	1.38	1.39	1.30
800.0	6.61	6.85	6.83	6.72	0.24	1.80	22.65	23.80	26.39	1.17	1.25	1.37	1.38	1.30
810.0	6.59	6.83	6.80	6.69	0.23	2.06	22.60	23.83	26.11	1.14	1.24	1.36	1.37	1.29
815.0	6.59	6.82	6.79	6.68	0.23	2.17	22.56	23.84	25.96	1.13	1.24	1.36	1.37	1.29
822.5	6.57	6.80	6.78	6.67	0.23	2.33	22.49	23.80	25.69	1.12	1.23	1.36	1.36	1.28
830.0	6.57	6.79	6.76	6.66	0.22	2.52	22.40	23.73	25.39	1.11	1.23	1.35	1.36	1.28
837.5	6.56	6.78	6.75	6.65	0.22	2.68	22.29	23.62	25.09	1.11	1.23	1.35	1.36	1.27
845.0	6.55	6.77	6.74	6.64	0.21	2.85	22.16	23.49	24.77	1.12	1.22	1.34	1.35	1.27
852.5	6.55	6.76	6.73	6.64	0.21	3.03	22.03	23.32	24.44	1.13	1.22	1.34	1.35	1.26
860.0	6.55	6.75	6.72	6.63	0.20	3.19	21.88	23.16	24.12	1.15	1.21	1.33	1.34	1.26
867.5	6.55	6.74	6.72	6.63	0.20	3.36	21.73	22.97	23.80	1.16	1.21	1.33	1.34	1.25
875.0	6.55	6.74	6.71	6.63	0.19	3.55	21.57	22.77	23.49	1.18	1.21	1.32	1.34	1.25
882.5	6.55	6.74	6.71	6.63	0.19	3.70	21.42	22.55	23.17	1.20	1.20	1.32	1.33	1.25
890.0	6.55	6.73	6.71	6.63	0.18	3.87	21.24	22.34	22.88	1.22	1.20	1.32	1.33	1.24
900.0	6.56	6.73	6.70	6.63	0.17	4.10	21.03	22.06	22.50	1.25	1.20	1.31	1.32	1.24
905.0	6.56	6.73	6.70	6.63	0.17	4.21	20.91	21.94	22.31	1.27	1.20	1.31	1.32	1.24
912.5	6.57	6.74	6.70	6.64	0.17	4.36	20.75	21.73	22.04	1.29	1.19	1.30	1.32	1.23
920.0	6.58	6.74	6.71	6.64	0.16	4.53	20.59	21.48	21.77	1.31	1.19	1.30	1.31	1.23
927.5	6.59	6.74	6.71	6.65	0.15	4.71	20.43	21.26	21.52	1.34	1.19	1.30	1.31	1.23
935.0	6.59	6.74	6.71	6.65	0.15	4.87	20.27	21.06	21.27	1.36	1.19	1.29	1.31	1.22
950.0	6.61	6.75	6.72	6.67	0.14	5.21	19.96	20.64	20.82	1.41	1.18	1.29	1.30	1.22
960.0	6.63	6.76	6.73	6.68	0.13	5.41	19.76	20.38	20.53	1.44	1.18	1.28	1.30	1.22

¹Total Loss = Insertion Loss + 6dB Splitter Loss

REV. X2

BP4C+

100623

Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



4 Way-0° Power Splitter/Combiner

BP4C+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = -40°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
560.0	9.11	9.52	9.51	9.31	0.41	4.73	14.99	14.29	15.82	4.02	1.42	1.51	1.51	1.50
567.5	8.94	9.34	9.34	9.13	0.40	4.49	15.21	14.51	16.08	3.83	1.41	1.51	1.51	1.50
575.0	8.78	9.17	9.17	8.97	0.40	4.23	15.45	14.75	16.35	3.64	1.41	1.51	1.51	1.49
582.5	8.62	9.01	9.00	8.80	0.39	3.99	15.69	14.99	16.64	3.47	1.40	1.51	1.51	1.49
590.0	8.46	8.85	8.85	8.65	0.39	3.74	15.94	15.24	16.94	3.31	1.40	1.51	1.51	1.48
597.5	8.32	8.70	8.69	8.50	0.38	3.52	16.20	15.50	17.25	3.16	1.39	1.51	1.51	1.48
605.0	8.18	8.56	8.55	8.36	0.38	3.30	16.46	15.77	17.57	3.02	1.39	1.50	1.51	1.47
612.5	8.05	8.42	8.42	8.23	0.37	3.06	16.74	16.06	17.91	2.88	1.38	1.50	1.51	1.46
620.0	7.93	8.30	8.29	8.10	0.37	2.84	17.02	16.35	18.26	2.76	1.38	1.50	1.51	1.46
627.5	7.81	8.18	8.17	7.98	0.36	2.62	17.31	16.65	18.62	2.64	1.38	1.50	1.50	1.45
635.0	7.70	8.06	8.05	7.87	0.36	2.41	17.61	16.96	19.00	2.53	1.37	1.49	1.50	1.45
642.5	7.60	7.95	7.94	7.76	0.35	2.19	17.91	17.28	19.40	2.43	1.37	1.49	1.50	1.44
650.0	7.50	7.84	7.83	7.66	0.34	1.95	18.21	17.61	19.80	2.33	1.36	1.49	1.50	1.43
657.5	7.40	7.74	7.73	7.56	0.34	1.73	18.52	17.94	20.22	2.23	1.35	1.48	1.49	1.42
665.0	7.31	7.65	7.64	7.47	0.33	1.53	18.84	18.29	20.66	2.14	1.35	1.48	1.49	1.42
672.5	7.24	7.56	7.55	7.38	0.33	1.35	19.15	18.64	21.10	2.06	1.34	1.47	1.48	1.41
680.0	7.15	7.47	7.47	7.30	0.32	1.11	19.47	19.00	21.56	1.98	1.34	1.47	1.48	1.40
687.5	7.08	7.40	7.39	7.23	0.31	0.90	19.78	19.37	22.03	1.91	1.33	1.46	1.48	1.40
695.0	7.01	7.32	7.31	7.16	0.31	0.72	20.08	19.74	22.51	1.84	1.32	1.46	1.47	1.39
702.5	6.95	7.25	7.24	7.09	0.30	0.61	20.39	20.10	22.99	1.77	1.32	1.45	1.47	1.38
710.0	6.89	7.19	7.18	7.03	0.30	0.50	20.69	20.48	23.47	1.71	1.31	1.45	1.46	1.37
717.5	6.83	7.13	7.12	6.97	0.30	0.36	20.97	20.86	23.94	1.65	1.31	1.44	1.46	1.37
725.0	6.78	7.07	7.06	6.92	0.29	0.38	21.24	21.22	24.42	1.59	1.30	1.44	1.45	1.36
732.5	6.74	7.02	7.01	6.87	0.29	0.47	21.49	21.58	24.88	1.54	1.30	1.43	1.45	1.36
740.0	6.70	6.98	6.96	6.82	0.28	0.56	21.72	21.94	25.30	1.49	1.29	1.43	1.44	1.35
747.5	6.66	6.93	6.92	6.78	0.28	0.73	21.93	22.27	25.67	1.44	1.29	1.43	1.44	1.34
755.0	6.62	6.89	6.88	6.74	0.28	0.91	22.11	22.59	26.01	1.40	1.28	1.42	1.43	1.34
762.5	6.59	6.86	6.84	6.71	0.27	1.11	22.27	22.88	26.28	1.36	1.28	1.42	1.43	1.33
770.0	6.56	6.83	6.81	6.68	0.27	1.28	22.39	23.15	26.48	1.32	1.27	1.41	1.42	1.32
777.5	6.53	6.80	6.78	6.65	0.26	1.44	22.50	23.38	26.59	1.28	1.27	1.41	1.42	1.32
785.0	6.51	6.77	6.75	6.62	0.26	1.62	22.57	23.56	26.63	1.25	1.26	1.40	1.41	1.31
792.5	6.49	6.74	6.72	6.60	0.25	1.82	22.61	23.72	26.61	1.22	1.26	1.40	1.41	1.31
800.0	6.47	6.72	6.70	6.58	0.25	2.03	22.61	23.82	26.49	1.19	1.25	1.39	1.40	1.30
810.0	6.45	6.69	6.67	6.56	0.24	2.26	22.57	23.89	26.23	1.16	1.25	1.38	1.39	1.30
815.0	6.45	6.68	6.66	6.55	0.24	2.41	22.54	23.89	26.07	1.15	1.24	1.38	1.39	1.29
822.5	6.43	6.67	6.65	6.54	0.23	2.58	22.48	23.88	25.82	1.13	1.24	1.38	1.38	1.29
830.0	6.43	6.65	6.63	6.52	0.23	2.78	22.39	23.82	25.50	1.12	1.23	1.37	1.38	1.28
837.5	6.42	6.64	6.62	6.51	0.23	2.94	22.28	23.74	25.20	1.11	1.23	1.36	1.37	1.28
845.0	6.41	6.63	6.61	6.50	0.22	3.08	22.16	23.61	24.91	1.12	1.23	1.36	1.37	1.27
852.5	6.41	6.62	6.59	6.50	0.21	3.28	22.05	23.39	24.60	1.12	1.22	1.35	1.36	1.27
860.0	6.40	6.61	6.59	6.49	0.21	3.46	21.89	23.21	24.23	1.14	1.22	1.35	1.36	1.26
867.5	6.40	6.61	6.58	6.49	0.20	3.64	21.74	23.02	23.90	1.15	1.22	1.35	1.36	1.26
875.0	6.40	6.60	6.58	6.49	0.20	3.81	21.57	22.82	23.56	1.17	1.21	1.34	1.35	1.25
882.5	6.41	6.60	6.57	6.48	0.19	3.98	21.40	22.61	23.25	1.19	1.21	1.34	1.35	1.25
890.0	6.41	6.60	6.57	6.48	0.19	4.16	21.23	22.39	22.93	1.21	1.21	1.33	1.34	1.24
900.0	6.41	6.60	6.57	6.49	0.18	4.40	21.00	22.11	22.54	1.24	1.20	1.33	1.34	1.24
905.0	6.42	6.60	6.57	6.49	0.18	4.51	20.89	21.99	22.37	1.25	1.20	1.33	1.34	1.24
912.5	6.43	6.60	6.57	6.49	0.17	4.65	20.72	21.74	22.06	1.28	1.20	1.32	1.33	1.23
920.0	6.43	6.60	6.57	6.50	0.17	4.87	20.55	21.51	21.79	1.30	1.20	1.32	1.33	1.23
927.5	6.44	6.60	6.57	6.50	0.16	5.05	20.39	21.29	21.53	1.32	1.19	1.32	1.33	1.23
935.0	6.45	6.60	6.57	6.51	0.16	5.22	20.23	21.07	21.28	1.35	1.19	1.31	1.32	1.23
950.0	6.47	6.61	6.58	6.53	0.15	5.57	19.91	20.65	20.81	1.40	1.19	1.31	1.32	1.22
960.0	6.48	6.62	6.59	6.54	0.14	5.75	19.71	20.38	20.52	1.43	1.18	1.30	1.31	1.22

¹Total Loss = Insertion Loss + 6dB Splitter Loss

REV. X2

BP4C+

100623

Page 2 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



4 Way-0° Power Splitter/Combiner

BP4C+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +85°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
560.0	9.19	9.60	9.59	9.42	0.41	5.31	15.41	14.70	16.27	3.76	1.42	1.52	1.51	1.52
567.5	9.02	9.43	9.41	9.25	0.40	5.27	15.63	14.93	16.54	3.59	1.42	1.52	1.51	1.51
575.0	8.86	9.26	9.25	9.09	0.40	5.25	15.87	15.17	16.82	3.43	1.41	1.52	1.51	1.50
582.5	8.71	9.10	9.09	8.93	0.39	5.21	16.12	15.41	17.11	3.27	1.41	1.51	1.51	1.49
590.0	8.56	8.95	8.93	8.79	0.39	5.18	16.37	15.67	17.42	3.13	1.40	1.51	1.50	1.49
597.5	8.42	8.80	8.78	8.64	0.38	5.14	16.63	15.93	17.73	2.99	1.40	1.51	1.50	1.48
605.0	8.28	8.66	8.64	8.51	0.38	5.13	16.89	16.20	18.06	2.86	1.39	1.50	1.50	1.47
612.5	8.15	8.52	8.51	8.38	0.37	5.09	17.17	16.49	18.40	2.74	1.39	1.50	1.49	1.47
620.0	8.03	8.40	8.38	8.26	0.36	5.08	17.44	16.78	18.75	2.62	1.38	1.49	1.49	1.46
627.5	7.92	8.28	8.26	8.14	0.36	5.06	17.73	17.08	19.12	2.51	1.37	1.49	1.48	1.45
635.0	7.81	8.16	8.15	8.03	0.36	5.03	18.02	17.39	19.50	2.41	1.37	1.48	1.48	1.44
642.5	7.70	8.05	8.04	7.93	0.35	5.01	18.31	17.71	19.90	2.31	1.36	1.47	1.47	1.44
650.0	7.61	7.95	7.93	7.83	0.34	4.99	18.61	18.03	20.30	2.22	1.35	1.47	1.47	1.43
657.5	7.51	7.85	7.84	7.73	0.34	4.98	18.91	18.36	20.72	2.13	1.35	1.46	1.46	1.42
665.0	7.43	7.76	7.74	7.65	0.33	4.97	19.21	18.70	21.14	2.05	1.34	1.46	1.46	1.41
672.5	7.35	7.67	7.66	7.57	0.33	4.95	19.52	19.04	21.59	1.97	1.33	1.45	1.45	1.41
680.0	7.27	7.59	7.58	7.49	0.33	4.96	19.82	19.40	22.03	1.90	1.33	1.44	1.45	1.40
687.5	7.20	7.52	7.50	7.42	0.32	4.94	20.11	19.75	22.50	1.83	1.32	1.44	1.44	1.39
695.0	7.13	7.44	7.43	7.35	0.31	4.92	20.41	20.10	22.94	1.77	1.31	1.43	1.44	1.38
702.5	7.07	7.38	7.36	7.28	0.31	4.92	20.69	20.46	23.40	1.71	1.31	1.43	1.43	1.37
710.0	7.01	7.31	7.30	7.23	0.30	4.90	20.96	20.82	23.87	1.65	1.30	1.42	1.43	1.37
717.5	6.96	7.26	7.24	7.17	0.30	4.91	21.22	21.16	24.30	1.59	1.30	1.42	1.42	1.36
725.0	6.91	7.20	7.19	7.12	0.29	5.00	21.47	21.51	24.74	1.54	1.29	1.41	1.41	1.35
732.5	6.87	7.15	7.14	7.07	0.29	5.16	21.69	21.85	25.13	1.49	1.28	1.40	1.41	1.34
740.0	6.83	7.11	7.09	7.03	0.28	5.29	21.89	22.16	25.50	1.45	1.28	1.40	1.41	1.34
747.5	6.79	7.07	7.05	6.99	0.28	5.46	22.07	22.46	25.81	1.40	1.27	1.39	1.40	1.33
755.0	6.75	7.03	7.01	6.95	0.27	5.65	22.24	22.74	26.08	1.36	1.27	1.39	1.39	1.32
762.5	6.72	6.99	6.97	6.92	0.27	5.81	22.36	23.00	26.30	1.32	1.26	1.38	1.39	1.32
770.0	6.69	6.96	6.94	6.89	0.26	5.96	22.46	23.22	26.38	1.29	1.26	1.37	1.38	1.31
777.5	6.67	6.93	6.91	6.87	0.26	6.12	22.54	23.40	26.45	1.25	1.25	1.37	1.38	1.30
785.0	6.65	6.90	6.88	6.84	0.25	6.28	22.58	23.56	26.43	1.22	1.25	1.36	1.37	1.30
792.5	6.63	6.87	6.85	6.82	0.25	6.44	22.61	23.66	26.34	1.19	1.24	1.36	1.37	1.29
800.0	6.61	6.85	6.83	6.80	0.24	6.61	22.59	23.73	26.22	1.17	1.24	1.35	1.36	1.29
810.0	6.59	6.83	6.80	6.78	0.23	6.87	22.55	23.75	25.96	1.14	1.24	1.34	1.35	1.28
815.0	6.59	6.82	6.79	6.77	0.23	6.97	22.51	23.75	25.80	1.13	1.23	1.34	1.35	1.28
822.5	6.57	6.80	6.78	6.76	0.23	7.14	22.44	23.70	25.53	1.12	1.23	1.33	1.35	1.27
830.0	6.57	6.79	6.76	6.74	0.22	7.33	22.34	23.64	25.25	1.11	1.22	1.33	1.34	1.27
837.5	6.56	6.78	6.75	6.73	0.22	7.48	22.24	23.54	24.95	1.11	1.22	1.32	1.34	1.26
845.0	6.55	6.77	6.74	6.73	0.21	7.64	22.13	23.40	24.69	1.12	1.22	1.32	1.33	1.26
852.5	6.55	6.76	6.73	6.72	0.21	7.81	22.00	23.20	24.37	1.13	1.21	1.31	1.33	1.25
860.0	6.55	6.75	6.72	6.71	0.20	7.97	21.85	23.03	24.04	1.15	1.21	1.31	1.32	1.25
867.5	6.55	6.74	6.72	6.71	0.20	8.15	21.70	22.85	23.73	1.16	1.21	1.31	1.32	1.25
875.0	6.55	6.74	6.71	6.71	0.19	8.30	21.55	22.66	23.42	1.18	1.20	1.30	1.31	1.24
882.5	6.55	6.74	6.71	6.71	0.19	8.47	21.39	22.46	23.12	1.20	1.20	1.30	1.31	1.24
890.0	6.55	6.73	6.71	6.71	0.18	8.62	21.23	22.25	22.83	1.22	1.20	1.29	1.31	1.23
900.0	6.56	6.73	6.70	6.71	0.17	8.83	21.02	22.00	22.47	1.25	1.19	1.29	1.30	1.23
905.0	6.56	6.73	6.70	6.71	0.17	8.92	20.91	21.85	22.29	1.27	1.19	1.29	1.30	1.23
912.5	6.57	6.74	6.70	6.72	0.17	9.08	20.75	21.64	22.01	1.29	1.19	1.28	1.30	1.22
920.0	6.58	6.74	6.71	6.72	0.16	9.24	20.59	21.43	21.76	1.31	1.19	1.28	1.29	1.22
927.5	6.59	6.74	6.71	6.73	0.15	9.40	20.44	21.22	21.51	1.34	1.19	1.27	1.29	1.22
935.0	6.59	6.74	6.71	6.73	0.15	9.55	20.28	21.02	21.28	1.36	1.18	1.27	1.28	1.22
950.0	6.61	6.75	6.72	6.75	0.14	9.88	19.99	20.62	20.83	1.41	1.18	1.27	1.28	1.21
960.0	6.63	6.76	6.73	6.76	0.13	10.07	19.80	20.36	20.56	1.44	1.18	1.26	1.27	1.21

¹Total Loss = Insertion Loss + 6dB Splitter Loss

REV. X2

BP4C+

100623

Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

