

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
10	39.42	1.03
20	39.42	1.03
30	39.47	1.03
40	39.48	1.03
50	39.47	1.03
60	39.52	1.03
70	39.53	1.03
80	39.50	1.03
90	39.46	1.04
100	39.54	1.04
150	39.55	1.04
200	39.59	1.05
250	39.57	1.05
300	39.61	1.06
350	39.58	1.06
400	39.70	1.07
450	39.67	1.07
500	39.74	1.08
550	39.80	1.08
600	39.76	1.09
650	39.79	1.09
700	39.81	1.10
750	39.89	1.10
800	39.97	1.11
850	39.95	1.11
900	40.00	1.12
950	40.05	1.12
1000	40.13	1.13
1100	40.17	1.14
1200	40.30	1.15
1300	40.32	1.16
1400	40.48	1.17
1500	40.51	1.18
1600	40.56	1.20
1700	40.77	1.21
1800	40.75	1.22
1900	40.85	1.23
2000	40.94	1.24
2100	41.02	1.25
2200	40.99	1.25
2300	41.08	1.26
2400	41.16	1.26
2500	41.20	1.27
2600	41.25	1.26
2700	41.25	1.26
2800	41.32	1.25
2900	41.37	1.23
3000	41.35	1.21
3100	41.53	1.19
3200	41.57	1.16
3300	41.54	1.14
3400	41.53	1.11
3500	41.63	1.09
3600	41.56	1.06
3700	41.64	1.04
3800	41.59	1.01
3900	41.58	1.03
4000	41.58	1.07