

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
2400	0.14	17.87	12.20	39.22	41.77	11.60
2402	0.14	17.86	12.19	39.26	41.78	11.60
2405	0.14	17.85	12.21	38.94	41.34	11.59
2408	0.14	17.85	12.21	39.11	41.31	11.58
2411	0.14	17.84	12.21	39.02	40.99	11.59
2414	0.14	17.83	12.20	38.78	40.66	11.58
2417	0.14	17.82	12.22	38.86	40.19	11.58
2420	0.14	17.81	12.22	38.68	39.94	11.57
2423	0.14	17.80	12.24	38.68	39.65	11.56
2426	0.14	17.79	12.24	38.66	39.60	11.56
2429	0.14	17.78	12.27	38.77	39.47	11.56
2432	0.14	17.78	12.26	38.37	39.10	11.55
2435	0.14	17.77	12.27	38.38	38.91	11.55
2438	0.14	17.76	12.30	38.29	38.55	11.55
2441	0.14	17.75	12.28	38.04	38.46	11.55
2444	0.14	17.75	12.30	38.02	38.25	11.55
2447	0.14	17.73	12.31	37.88	37.84	11.55
2450	0.14	17.72	12.31	37.85	37.68	11.54
2452	0.14	17.72	12.31	37.89	37.52	11.54
2455	0.14	17.71	12.32	37.68	37.47	11.53
2458	0.15	17.71	12.33	37.55	37.30	11.53
2461	0.15	17.70	12.33	37.48	37.04	11.53
2464	0.14	17.69	12.35	37.24	36.88	11.53
2467	0.15	17.68	12.35	37.02	36.74	11.53
2470	0.14	17.67	12.37	36.94	36.69	11.53
2473	0.15	17.66	12.37	36.78	36.42	11.52
2476	0.14	17.65	12.38	36.61	36.35	11.52
2479	0.15	17.64	12.38	36.62	36.18	11.52
2482	0.15	17.63	12.39	36.55	36.23	11.52
2485	0.15	17.63	12.38	36.30	35.98	11.51
2488	0.15	17.62	12.40	36.17	35.83	11.51
2491	0.15	17.61	12.41	36.16	35.91	11.50
2494	0.15	17.60	12.40	36.00	35.64	11.50
2497	0.15	17.59	12.41	35.91	35.60	11.50
2500	0.15	17.58	12.41	35.83	35.49	11.49