

## Typical Performance Data

FREQUENCY (MHz)	PHASE SHIFT		RETURN LOSS					
	(Deg.)		(dBr)					
	0°C	50°C	Vc=0.5V @ 0°C	Vc=10V @ 0°C	Vc=25V @ 0°C	Vc=0.5V @ +50°C	Vc=10V @ +50°C	Vc=25V @ +50°C
300.0	290.51	299.06	-10.83	-9.85	-9.63	-11.40	-9.90	-9.73
360.0	365.70	374.24	-10.79	-10.10	-9.72	-11.21	-10.20	-9.76
420.0	402.47	408.38	-10.86	-10.39	-9.90	-11.17	-10.38	-10.04
480.0	412.55	416.59	-10.98	-10.31	-10.29	-11.20	-10.40	-10.32
520.0	409.93	413.82	-10.93	-10.12	-10.46	-11.17	-10.33	-10.48
580.0	403.67	408.94	-10.78	-9.87	-10.43	-10.99	-10.04	-10.46
640.0	402.14	408.69	-10.48	-9.72	-10.14	-10.74	-10.04	-10.16
700.0	403.23	410.19	-10.14	-9.96	-9.81	-10.38	-10.30	-9.89
760.0	403.87	410.63	-9.87	-10.80	-9.60	-10.13	-11.70	-9.71
800.0	402.32	409.49	-9.75	-11.66	-9.45	-9.97	-11.88	-9.58
880.0	397.09	402.32	-9.72	-11.35	-9.44	-9.92	-11.42	-9.59
920.0	394.06	394.63	-9.74	-10.78	-9.52	-9.91	-10.96	-9.70
980.0	374.13	377.19	-9.82	-10.11	-9.90	-9.96	-10.33	-10.16
1040.0	343.98	345.70	-9.91	-9.69	-10.69	-10.05	-9.91	-10.98
1100.0	293.33	294.33	-10.04	-9.40	-11.73	-10.19	-9.63	-11.96