

Fixed Attenuator

FW-4+

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
10.0	4.00	1.01
50.0	4.02	1.01
100.0	4.03	1.01
500.0	4.09	1.01
1000.0	4.12	1.01
1200.0	4.13	1.01
1400.0	4.15	1.01
1600.0	4.16	1.01
1800.0	4.17	1.01
2000.0	4.18	1.01
2200.0	4.20	1.00
2400.0	4.20	1.00
2600.0	4.22	1.01
2800.0	4.23	1.01
3000.0	4.24	1.02
3200.0	4.25	1.03
3400.0	4.26	1.04
3600.0	4.28	1.05
3800.0	4.29	1.06
4000.0	4.29	1.07
4200.0	4.31	1.08
4400.0	4.32	1.08
4600.0	4.33	1.09
4800.0	4.34	1.09
5000.0	4.35	1.10
5200.0	4.37	1.10
5500.0	4.38	1.10
6000.0	4.40	1.09
6500.0	4.42	1.08
7000.0	4.45	1.08
7500.0	4.49	1.11
8000.0	4.51	1.14
8500.0	4.55	1.17
9000.0	4.57	1.20
9500.0	4.63	1.23
10000.0	4.66	1.26
10500.0	4.64	1.28
11000.0	4.66	1.28
11500.0	4.70	1.29
12000.0	4.72	1.31
12500.0	4.73	1.30
13000.0	4.71	1.30
13500.0	4.71	1.28
14000.0	4.71	1.26
14500.0	4.68	1.22
15000.0	4.70	1.18



P.O. Box 350166, Brooklyn, New York 11235-0003 • (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS



REV. OR
FW-4+
5/1/2014
Page 1 of 1