

*Typical Performance Data*

FREQ.	ATTENUATION	VSWR
(MHz)	(dB)	(:1)
10	8.00	1.12
20	8.01	1.12
50	8.02	1.12
80	8.03	1.12
100	8.04	1.12
120	8.04	1.12
150	8.05	1.12
180	8.06	1.12
210	8.06	1.12
240	8.07	1.12
270	8.07	1.12
300	8.08	1.12
330	8.08	1.12
360	8.08	1.13
390	8.09	1.13
420	8.09	1.13
450	8.10	1.13
480	8.10	1.13
500	8.10	1.13
530	8.11	1.13
560	8.11	1.14
590	8.12	1.14
620	8.12	1.14
650	8.12	1.14
680	8.13	1.14
710	8.14	1.14
750	8.14	1.14
780	8.14	1.15
810	8.15	1.15
840	8.15	1.15
890	8.16	1.15
920	8.16	1.15
950	8.16	1.15
980	8.17	1.16
1000	8.17	1.16
1030	8.17	1.16
1050	8.18	1.16
1080	8.18	1.16
1110	8.18	1.16
1150	8.19	1.16
1180	8.19	1.16
1200	8.19	1.16
1230	8.19	1.16
1250	8.20	1.16
1280	8.20	1.16
1300	8.20	1.16
1350	8.21	1.16
1400	8.21	1.16
1450	8.21	1.16
1500	8.22	1.16
1550	8.23	1.16
1600	8.23	1.16
1650	8.23	1.16
1700	8.24	1.16
1750	8.24	1.16
1800	8.25	1.15
1850	8.25	1.15
1900	8.25	1.15
1950	8.26	1.15
2000	8.26	1.14