

*Typical Performance Data*

FREQ.	ATTENUATION	VSWR
(MHz)	(dB)	(:1)
10	8.95	1.11
20	8.95	1.11
50	8.96	1.11
80	8.97	1.11
100	8.98	1.11
120	8.98	1.11
150	8.99	1.11
180	8.99	1.11
210	9.00	1.11
240	9.00	1.11
270	9.01	1.11
300	9.01	1.11
330	9.02	1.11
360	9.02	1.11
390	9.03	1.11
420	9.03	1.12
450	9.03	1.12
480	9.04	1.12
500	9.04	1.12
530	9.04	1.12
560	9.05	1.13
590	9.05	1.13
620	9.06	1.13
650	9.06	1.13
680	9.06	1.13
710	9.07	1.14
750	9.07	1.14
780	9.08	1.14
810	9.08	1.14
840	9.08	1.14
890	9.09	1.15
920	9.10	1.15
950	9.10	1.15
980	9.10	1.15
1000	9.11	1.15
1030	9.11	1.15
1050	9.11	1.15
1080	9.11	1.16
1110	9.12	1.16
1150	9.12	1.16
1180	9.13	1.16
1200	9.13	1.16
1230	9.13	1.16
1250	9.13	1.16
1280	9.13	1.16
1300	9.14	1.16
1350	9.14	1.16
1400	9.15	1.17
1450	9.15	1.17
1500	9.16	1.17
1550	9.16	1.17
1600	9.17	1.17
1650	9.17	1.16
1700	9.18	1.16
1750	9.18	1.16
1800	9.19	1.16
1850	9.19	1.16
1900	9.19	1.15
1950	9.20	1.15
2000	9.20	1.15