

*Typical Performance Data*

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | RETURN<br>LOSS<br>(dB) |
|--------------------|---------------------------|------------------------|
| 200.00             | 3.14                      | 3.26                   |
| 225.00             | 2.78                      | 3.68                   |
| 250.00             | 2.50                      | 4.07                   |
| 275.00             | 2.28                      | 4.41                   |
| 300.00             | 2.14                      | 4.72                   |
| 325.00             | 2.02                      | 4.97                   |
| 350.00             | 1.89                      | 5.20                   |
| 375.00             | 1.81                      | 5.40                   |
| 400.00             | 1.77                      | 5.56                   |
| 425.00             | 1.72                      | 5.71                   |
| 450.00             | 1.65                      | 5.83                   |
| 475.00             | 1.63                      | 5.92                   |
| 500.00             | 1.63                      | 5.99                   |
| 525.00             | 1.60                      | 6.06                   |
| 550.00             | 1.58                      | 6.11                   |
| 575.00             | 1.60                      | 6.16                   |
| 600.00             | 1.60                      | 6.17                   |
| 625.00             | 1.59                      | 6.20                   |
| 650.00             | 1.60                      | 6.20                   |
| 675.00             | 1.63                      | 6.20                   |
| 700.00             | 1.63                      | 6.19                   |
| 725.00             | 1.64                      | 6.19                   |
| 750.00             | 1.67                      | 6.16                   |
| 775.00             | 1.68                      | 6.14                   |
| 800.00             | 1.73                      | 6.13                   |
| 825.00             | 1.75                      | 6.11                   |
| 850.00             | 1.73                      | 6.09                   |
| 875.00             | 1.77                      | 6.06                   |
| 900.00             | 1.86                      | 6.04                   |
| 925.00             | 1.86                      | 6.03                   |
| 950.00             | 1.81                      | 6.02                   |
| 975.00             | 1.88                      | 5.99                   |
| 1000.00            | 2.01                      | 5.98                   |
| 1025.00            | 1.99                      | 5.96                   |
| 1050.00            | 1.92                      | 5.95                   |
| 1075.00            | 2.01                      | 5.95                   |
| 1100.00            | 2.12                      | 5.95                   |
| 1125.00            | 2.10                      | 5.95                   |
| 1150.00            | 2.08                      | 5.95                   |