

Ceramic High Pass Filter

HFCN-3500D+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	59.91	60.08	58.78	0.03	0.02	0.02	0.01	0.01	0.01
100	53.31	53.23	52.94	0.04	0.03	0.03	0.02	0.01	0.01
200	47.47	47.26	47.04	0.03	0.01	0.00	0.01	0.01	0.02
500	39.77	39.85	39.83	0.04	0.01	0.02	0.03	0.00	0.02
1000	35.91	35.96	36.12	0.01	0.05	0.09	0.00	0.05	0.08
1500	37.56	37.96	38.36	0.07	0.14	0.19	0.07	0.13	0.17
2000	52.98	49.79	47.86	0.19	0.27	0.33	0.14	0.23	0.26
2500	32.40	32.26	32.25	0.29	0.38	0.45	0.29	0.39	0.45
2800	34.36	35.48	36.63	0.32	0.44	0.52	0.42	0.56	0.66
2850	36.84	38.30	38.86	0.40	0.52	0.61	0.43	0.59	0.70
2900	39.48	38.50	35.95	0.41	0.55	0.65	0.43	0.59	0.71
3000	31.05	28.37	26.19	0.46	0.62	0.74	0.53	0.73	0.88
3100	22.70	20.92	19.38	0.57	0.76	0.93	0.63	0.88	1.09
3200	16.41	15.06	13.86	0.81	1.09	1.35	0.94	1.29	1.62
3300	11.15	10.09	9.18	1.27	1.71	2.17	1.50	2.04	2.57
3400	6.88	6.16	5.57	2.47	3.23	4.02	2.85	3.76	4.68
3500	3.73	3.41	3.17	4.96	6.16	7.37	5.75	7.31	8.83
3650	1.53	1.63	1.69	12.17	13.49	14.91	15.91	20.02	24.94
3700	1.27	1.40	1.51	14.62	15.34	16.33	22.33	27.80	30.47
3900	0.98	1.18	1.31	14.21	13.69	13.76	15.90	15.01	14.66
4000	0.93	1.13	1.26	13.21	12.85	12.91	14.06	13.52	13.34
4500	0.76	0.93	1.08	13.76	13.97	13.82	13.80	13.98	13.76
5000	0.61	0.77	0.92	19.17	18.90	18.30	18.43	18.39	18.05
5500	0.56	0.73	0.91	26.53	27.15	25.99	22.43	23.92	23.45
6000	0.57	0.74	0.88	39.85	34.15	35.48	27.43	25.54	25.15
7000	0.50	0.71	0.90	24.07	24.40	25.80	23.44	23.22	23.17
8000	0.42	0.62	0.79	23.33	28.95	30.21	23.70	37.59	29.16
8800	0.44	0.76	1.09	20.66	19.30	18.08	19.25	18.15	15.93
9300	1.21	1.15	1.32	21.47	19.00	17.46	12.44	14.82	15.22
9500	0.96	1.29	1.56	15.29	14.70	13.92	13.09	13.90	13.43
9800	1.21	1.30	1.45	10.58	10.61	10.78	9.84	10.52	11.24
11000	1.62	2.11	2.42	7.16	6.69	6.75	7.46	6.87	6.86
12050	2.19	2.69	3.11	6.28	5.87	5.64	6.49	6.03	5.57
13000	2.56	2.29	2.51	5.81	7.72	8.50	5.61	7.71	7.88
14300	4.56	5.68	6.73	6.50	6.40	6.24	5.20	5.79	5.61
14600	9.11	10.48	11.53	3.64	4.15	4.60	3.38	4.29	5.33
16000	10.19	10.02	9.85	3.34	4.24	4.60	6.05	4.80	4.90
17000	5.35	7.24	8.98	7.10	6.57	6.62	9.90	6.07	4.37
18000	8.88	9.66	11.31	5.94	4.87	4.90	4.22	4.47	3.49
19000	9.64	10.28	11.63	6.72	4.50	3.56	2.43	3.59	4.40
20000	11.33	11.76	10.86	2.43	3.08	4.06	1.77	2.42	4.19

REV. X1

HFCN-3500D+

080723

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

