

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10	76.41	0.00
55	66.83	0.00
100	62.35	0.00
200	59.49	0.01
300	66.91	0.03
400	56.80	0.04
500	46.14	0.06
600	39.80	0.09
700	35.15	0.13
800	31.46	0.17
900	28.46	0.21
1000	25.95	0.26
1100	23.89	0.32
1200	22.32	0.38
1300	21.38	0.46
1400	21.64	0.56
1500	25.51	0.69
1600	24.02	0.99
1700	9.28	2.41
1800	2.67	9.20
1900	1.21	27.52
2000	0.99	18.31
2073	0.90	17.64
2100	0.87	17.87
2150	0.83	18.80
2200	0.78	20.19
2250	0.75	21.75
2300	0.72	23.19
2350	0.70	24.32
2400	0.69	24.78
2450	0.69	24.53
2500	0.69	24.09
2550	0.69	23.68
2600	0.70	23.38
2650	0.70	23.30
2700	0.71	23.44
2750	0.71	23.69
2800	0.72	24.05
2850	0.74	24.50
2900	0.75	24.91
2950	0.75	25.50
3000	0.79	26.13
3050	0.80	26.65
3100	0.83	27.26
3200	0.92	25.70
3400	1.55	11.95
3600	4.30	4.19
3800	9.74	1.48
4000	15.98	0.74
4146	20.52	0.54
4200	22.20	0.49
4400	28.64	0.39
4600	36.37	0.34
4800	51.28	0.29
5000	45.37	0.27
5200	39.56	0.25
5400	37.02	0.24
5600	35.48	0.23
5800	34.42	0.23
6000	33.62	0.23
6200	32.93	0.24
6400	32.40	0.25
6600	31.92	0.26
6800	31.46	0.28
7000	31.12	0.29
7200	30.78	0.31
7400	30.58	0.33
7600	30.50	0.35
7800	30.68	0.36
8000	31.18	0.35
8600	33.77	0.29
8800	30.27	0.30
9000	30.95	0.23
9600	30.31	0.20
10000	29.70	0.21

