

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
100	95.48	0.13
500	85.43	0.31
1000	78.83	0.43
2000	73.60	0.52
3000	70.89	0.45
4000	70.29	0.41
5000	70.08	0.49
6000	71.41	0.57
7000	72.09	0.63
8000	77.96	0.69
9000	74.51	0.79
10000	61.52	0.92
11000	53.06	1.11
12000	47.31	1.25
13000	44.05	1.33
14000	45.33	1.38
15000	36.58	1.43
16000	10.48	2.82
16600	1.46	22.44
17000	1.01	22.56
17700	0.98	14.54
18200	0.99	13.18
18600	0.86	16.39
19000	0.80	21.88
19300	0.85	19.48
19800	0.97	15.71
20200	0.98	16.82
20600	0.96	22.29
21000	1.06	21.33
21400	1.32	15.09
22000	1.70	16.66
23000	11.86	2.89
24000	30.91	1.90
25000	50.23	2.02
26000	45.91	2.15
27000	51.67	2.09
28000	63.02	1.91
29000	59.11	1.77
30000	54.32	1.70
31000	52.39	1.71
32000	54.76	1.84
33000	59.64	1.98
34000	57.70	2.16
35000	53.74	2.29
36000	51.33	2.38
37000	50.28	2.27
38000	49.33	2.14
39000	48.21	2.08
40000	46.89	2.11