

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10	72.13	0.00
50	70.15	0.00
500	69.23	0.02
800	65.21	0.03
1000	64.41	0.05
1200	66.18	0.06
1400	72.01	0.08
1600	72.26	0.09
1800	81.08	0.10
2000	67.69	0.11
2200	62.49	0.12
2400	58.74	0.12
2600	56.26	0.12
2800	54.88	0.13
3000	53.22	0.13
3200	51.41	0.13
3400	50.72	0.14
3600	51.60	0.16
3800	53.94	0.20
4000	64.27	0.28
4200	47.38	0.45
4330	50.82	0.71
4400	35.70	1.03
4440	26.83	1.36
4500	15.44	2.58
4600	3.97	13.69
4800	2.19	18.22
4810	2.18	17.93
4820	2.16	17.72
4830	2.15	17.64
4840	2.14	17.64
4850	2.13	17.75
4860	2.13	17.89
4870	2.13	18.10
4880	2.13	18.34
4890	2.13	18.53
4900	2.15	18.72
5000	2.56	19.36
5200	14.85	1.87
5375	39.20	0.61
5400	33.73	0.53
5600	30.36	0.29
5800	31.15	0.22
5900	31.91	0.21
6000	32.64	0.20
6200	34.08	0.20
6400	35.00	0.21
6600	36.08	0.22
6800	37.04	0.24
7000	37.73	0.27
7200	38.38	0.29
7400	39.31	0.31
7600	40.27	0.31
7800	40.12	0.33
8000	39.97	0.34
8200	39.11	0.37
8400	37.34	0.41
8600	35.85	0.48
8800	34.24	0.51
9000	33.38	0.51
9200	32.74	0.51
9400	32.38	0.49
9600	32.23	0.49
9800	31.80	0.50
10000	31.46	0.48
10200	31.18	0.46
10400	30.94	0.46
10600	30.80	0.46
10800	30.40	0.46
11000	29.96	0.46
11200	29.42	0.50
11400	28.79	0.50
11600	28.36	0.54
12000	28.08	0.63
12200	27.66	0.65
12600	27.58	0.71
12750	27.43	0.73