

Coaxial High Pass Filter

BHP-25+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	67.19	0.16	10.0	40.110
11.0	68.52	0.15	11.0	34.820
12.0	58.67	0.11	12.0	31.930
13.0	53.20	0.20	13.0	29.960
14.0	48.60	0.20	14.0	28.870
15.0	43.62	0.33	15.0	28.340
16.0	38.71	0.34	16.0	25.810
17.0	34.04	0.29	17.0	24.890
18.0	29.51	0.38	18.0	28.840
19.0	24.95	0.38	19.0	34.670
20.0	20.28	0.41	20.0	42.290
21.0	15.75	0.51	21.0	49.590
22.0	11.18	0.80	22.0	56.230
23.0	6.87	1.61	23.0	61.460
24.0	3.39	3.72	24.0	64.480
25.0	1.37	8.53	25.0	65.120
26.0	0.66	18.20	26.0	63.250
27.0	0.47	26.43	27.0	59.200
28.0	0.45	18.63	28.0	53.280
29.0	0.42	17.01	29.0	46.470
30.0	0.39	17.14	30.0	40.060
50.0	0.25	19.33	50.0	9.870
100.0	0.18	30.73	100.0	2.500
150.0	0.20	25.92	150.0	1.260
200.0	0.21	23.84	200.0	0.850
250.0	0.23	22.80	250.0	0.650
300.0	0.24	21.78	300.0	0.550
350.0	0.27	20.86	350.0	0.480
400.0	0.28	19.97	400.0	0.440
450.0	0.30	19.15	450.0	0.410
500.0	0.32	18.38	500.0	0.400
550.0	0.35	17.74	550.0	0.380
600.0	0.36	17.04	600.0	0.370
650.0	0.39	16.51	650.0	0.350
700.0	0.41	15.88	700.0	0.340
750.0	0.43	15.38	750.0	0.340
800.0	0.45	14.89	800.0	0.340
850.0	0.48	14.47	850.0	0.330
900.0	0.50	14.06	900.0	0.330
950.0	0.53	13.72	950.0	0.320
1000.0	0.55	13.37	1000.0	0.330
1500.0	0.82	11.30	1500.0	0.310
1960.0	1.22	10.99	1960.0	0.310
2420.0	1.45	12.78	2420.0	0.310

REV. X1
BHP-25+
061112
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

