

Coaxial High Pass Filter

BHP-600+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	74.47	0.04	200.0	0.760
100.0	89.80	0.05	250.0	0.620
200.0	72.58	0.07	300.0	0.840
250.0	63.01	0.12	350.0	0.980
300.0	53.56	0.12	360.0	1.010
350.0	44.05	0.18	362.0	1.020
360.0	42.15	0.18	364.0	0.990
362.0	41.76	0.18	366.0	1.000
364.0	41.37	0.18	368.0	1.000
366.0	40.99	0.19	370.0	0.990
368.0	40.60	0.19	372.0	1.020
370.0	40.22	0.19	374.0	1.050
372.0	39.82	0.18	376.0	1.060
374.0	39.45	0.19	400.0	1.170
376.0	39.06	0.19	410.0	1.250
400.0	34.36	0.20	420.0	1.270
410.0	32.39	0.22	430.0	1.350
420.0	30.45	0.19	440.0	1.440
430.0	28.45	0.21	450.0	1.510
440.0	26.44	0.23	460.0	1.630
450.0	24.44	0.33	465.0	1.720
460.0	22.38	0.35	470.0	1.800
465.0	21.34	0.37	475.0	1.890
470.0	20.29	0.39	500.0	2.450
475.0	19.23	0.42	505.0	2.590
500.0	13.91	0.68	510.0	2.760
510.0	11.76	0.90	515.0	2.960
520.0	9.64	1.23	520.0	3.170
525.0	8.60	1.46	525.0	3.400
545.0	4.82	3.18	545.0	4.390
551.0	3.88	4.10	551.0	4.630
557.0	3.07	5.28	557.0	4.760
564.0	2.30	7.09	564.0	4.780
570.0	1.79	9.07	570.0	4.680
577.0	1.35	12.04	577.0	4.460
583.0	1.09	15.36	583.0	4.210
590.0	0.89	20.77	590.0	3.900
600.0	0.72	29.98	600.0	3.490
650.0	0.56	15.56	650.0	2.290
700.0	0.46	18.08	700.0	1.850
750.0	0.41	25.35	750.0	1.570
800.0	0.40	33.79	800.0	1.350
850.0	0.39	30.47	850.0	1.190
900.0	0.36	30.63	900.0	1.070
950.0	0.35	32.35	950.0	0.970
1000.0	0.33	29.54	1000.0	0.880
1500.0	0.51	13.91	1500.0	0.520
2000.0	0.52	14.20	2000.0	0.410
2500.0	0.50	15.23	2500.0	0.370
3000.0	0.58	14.47	3000.0	0.350

REV. X1
BHP-600+
070628
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

