

4 Way-0° Power Splitter/Combiner

BP4U+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
1500	8.02	9.32	9.40	8.88	1.38	5.90	16.08	17.40	19.86	3.69	1.31	1.52	1.55	1.59
1550	7.66	8.92	9.00	8.50	1.33	4.63	16.71	18.10	20.82	3.26	1.28	1.48	1.51	1.54
1560	7.60	8.84	8.92	8.43	1.33	4.38	16.84	18.25	21.03	3.18	1.27	1.47	1.50	1.53
1570	7.53	8.77	8.85	8.36	1.32	4.13	16.98	18.41	21.25	3.10	1.27	1.47	1.49	1.52
1580	7.47	8.69	8.77	8.29	1.31	3.89	17.12	18.56	21.46	3.03	1.26	1.46	1.48	1.51
1590	7.40	8.62	8.70	8.22	1.30	3.65	17.27	18.72	21.69	2.95	1.25	1.45	1.47	1.51
1600	7.34	8.55	8.63	8.16	1.29	3.42	17.41	18.88	21.92	2.88	1.25	1.44	1.46	1.50
1650	7.06	8.23	8.31	7.86	1.24	2.19	18.18	19.79	23.20	2.56	1.22	1.40	1.42	1.45
1660	7.01	8.17	8.25	7.80	1.24	1.95	18.35	19.98	23.49	2.50	1.21	1.39	1.41	1.44
1670	6.96	8.11	8.19	7.76	1.23	1.74	18.52	20.18	23.78	2.44	1.21	1.38	1.40	1.44
1680	6.92	8.06	8.14	7.70	1.22	1.57	18.69	20.39	24.08	2.39	1.20	1.38	1.39	1.43
1690	6.87	8.00	8.08	7.65	1.21	1.47	18.87	20.60	24.40	2.33	1.20	1.37	1.38	1.42
1700	6.83	7.95	8.03	7.60	1.20	1.37	19.05	20.83	24.72	2.28	1.19	1.36	1.37	1.41
1750	6.62	7.71	7.78	7.38	1.16	0.99	19.99	22.00	26.48	2.04	1.16	1.32	1.33	1.37
1760	6.59	7.66	7.74	7.34	1.15	1.07	20.19	22.27	26.87	1.99	1.15	1.31	1.32	1.36
1770	6.55	7.62	7.69	7.31	1.14	1.27	20.38	22.54	27.26	1.95	1.15	1.30	1.32	1.35
1780	6.52	7.58	7.65	7.27	1.13	1.53	20.60	22.82	27.67	1.91	1.14	1.30	1.31	1.34
1790	6.49	7.54	7.61	7.24	1.12	1.74	20.81	23.09	28.11	1.87	1.14	1.29	1.30	1.33
1800	6.46	7.50	7.57	7.20	1.11	2.00	21.03	23.37	28.55	1.83	1.13	1.28	1.29	1.32
1850	6.32	7.33	7.39	7.04	1.08	3.26	22.15	24.95	30.69	1.65	1.10	1.24	1.25	1.29
1860	6.30	7.30	7.36	7.02	1.07	3.48	22.39	25.30	31.11	1.62	1.10	1.24	1.24	1.28
1870	6.27	7.27	7.33	6.99	1.06	3.72	22.62	25.66	31.53	1.59	1.10	1.23	1.23	1.27
1880	6.25	7.24	7.31	6.97	1.05	3.97	22.86	26.00	31.87	1.56	1.09	1.22	1.22	1.26
1890	6.23	7.21	7.28	6.95	1.05	4.22	23.12	26.37	32.15	1.53	1.08	1.22	1.21	1.26
1900	6.21	7.18	7.25	6.92	1.04	4.43	23.37	26.75	32.41	1.50	1.08	1.21	1.21	1.25
1950	6.13	7.06	7.13	6.83	1.00	3.74	24.67	28.84	32.52	1.36	1.06	1.18	1.17	1.21
1960	6.12	7.04	7.11	6.81	0.99	3.96	24.94	29.24	32.31	1.34	1.05	1.17	1.16	1.21
1970	6.10	7.02	7.10	6.80	0.99	6.05	25.21	29.64	32.04	1.32	1.05	1.17	1.16	1.20
1980	6.09	7.01	7.08	6.79	0.98	6.29	25.47	30.06	31.72	1.29	1.05	1.16	1.15	1.19
1990	6.08	6.99	7.06	6.78	0.98	6.52	25.73	30.50	31.36	1.27	1.04	1.16	1.14	1.19
2000	6.07	6.97	7.04	6.76	0.97	6.74	26.00	30.93	31.00	1.25	1.04	1.15	1.14	1.18
2050	6.04	6.91	6.97	6.72	0.93	7.92	27.29	32.39	29.09	1.15	1.03	1.13	1.10	1.15
2060	6.04	6.90	6.97	6.71	0.93	8.15	27.53	32.52	28.69	1.13	1.03	1.13	1.10	1.14
2070	6.03	6.89	6.96	6.71	0.92	8.35	27.75	32.60	28.30	1.12	1.03	1.12	1.10	1.14
2080	6.03	6.88	6.95	6.70	0.92	8.53	27.97	32.54	27.94	1.10	1.03	1.12	1.09	1.13
2090	6.02	6.87	6.93	6.70	0.91	8.74	28.17	32.47	27.58	1.09	1.04	1.12	1.09	1.13
2100	6.02	6.86	6.93	6.69	0.91	8.95	28.36	32.31	27.27	1.08	1.04	1.12	1.08	1.12
2120	6.02	6.84	6.91	6.69	0.89	9.40	28.72	31.79	26.58	1.06	1.05	1.11	1.08	1.11
2160	6.02	6.82	6.89	6.69	0.87	10.26	29.14	30.36	25.40	1.08	1.06	1.11	1.07	1.09
2180	6.03	6.82	6.88	6.69	0.85	10.71	29.22	29.64	24.87	1.11	1.07	1.11	1.07	1.08
2200	6.03	6.81	6.88	6.69	0.85	11.15	29.21	28.90	24.38	1.14	1.07	1.11	1.07	1.07
2240	6.06	6.82	6.89	6.71	0.83	12.03	28.98	27.48	23.46	1.20	1.09	1.11	1.08	1.06
2260	6.07	6.82	6.90	6.72	0.83	12.42	28.75	26.87	23.06	1.23	1.09	1.12	1.09	1.05
2280	6.08	6.83	6.90	6.74	0.82	12.84	28.49	26.23	22.68	1.26	1.10	1.12	1.10	1.05
2320	6.11	6.84	6.92	6.77	0.80	13.61	27.90	25.09	21.96	1.33	1.12	1.13	1.12	1.04
2340	6.13	6.85	6.92	6.79	0.79	13.97	27.58	24.61	21.63	1.37	1.12	1.14	1.13	1.04
2380	6.18	6.87	6.94	6.83	0.77	14.70	26.89	23.68	20.99	1.44	1.14	1.15	1.15	1.05
2400	6.20	6.89	6.96	6.85	0.76	15.10	26.55	23.25	20.70	1.47	1.15	1.16	1.16	1.05
2440	6.25	6.92	6.99	6.90	0.75	15.90	25.89	22.47	20.17	1.54	1.16	1.18	1.18	1.06
2480	6.30	6.96	7.03	6.95	0.74	16.60	25.26	21.77	19.67	1.61	1.17	1.20	1.20	1.07
2500	6.32	6.98	7.05	6.98	0.73	16.94	24.97	21.43	19.44	1.65	1.18	1.21	1.21	1.08
2550	6.39	7.03	7.10	7.04	0.71	17.79	24.26	20.63	18.88	1.74	1.20	1.23	1.24	1.09
2600	6.46	7.08	7.16	7.11	0.70	18.67	23.59	19.90	18.38	1.83	1.21	1.26	1.27	1.11

¹Total Loss = Insertion Loss + 6dB Splitter Loss

REV. X2
BP4U+
100705
Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



4 Way-0° Power Splitter/Combiner

BP4U+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = -40°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
1500	7.92	9.20	9.29	8.78	1.36	5.28	15.88	17.14	19.59	3.92	1.32	1.54	1.57	1.60
1550	7.55	8.79	8.88	8.39	1.32	3.91	16.49	17.83	20.52	3.43	1.30	1.50	1.53	1.56
1560	7.49	8.71	8.80	8.31	1.31	3.66	16.63	17.98	20.72	3.34	1.29	1.49	1.52	1.55
1570	7.42	8.63	8.73	8.24	1.30	3.59	16.76	18.13	20.93	3.25	1.29	1.48	1.51	1.54
1580	7.35	8.55	8.64	8.17	1.29	3.42	16.89	18.28	21.16	3.17	1.28	1.47	1.50	1.53
1590	7.29	8.48	8.57	8.10	1.28	3.30	17.03	18.43	21.37	3.09	1.27	1.46	1.50	1.53
1600	7.22	8.41	8.50	8.03	1.27	3.19	17.17	18.59	21.59	3.01	1.26	1.45	1.49	1.52
1650	6.94	8.09	8.18	7.73	1.24	2.63	17.93	19.46	22.82	2.67	1.23	1.41	1.44	1.47
1660	6.89	8.03	8.12	7.68	1.23	2.54	18.09	19.66	23.10	2.61	1.22	1.40	1.43	1.46
1670	6.85	7.97	8.06	7.63	1.22	2.44	18.26	19.84	23.38	2.55	1.22	1.40	1.42	1.45
1680	6.80	7.92	8.01	7.58	1.21	2.33	18.43	20.05	23.67	2.49	1.21	1.39	1.41	1.44
1690	6.75	7.86	7.95	7.52	1.20	2.22	18.60	20.25	23.97	2.43	1.20	1.39	1.40	1.43
1700	6.70	7.82	7.90	7.47	1.19	2.12	18.78	20.45	24.29	2.38	1.20	1.38	1.40	1.42
1750	6.49	7.56	7.64	7.24	1.15	2.82	19.71	21.60	25.99	2.11	1.17	1.34	1.35	1.38
1760	6.45	7.51	7.59	7.20	1.14	2.98	19.90	21.84	26.38	2.06	1.17	1.33	1.34	1.38
1770	6.42	7.46	7.55	7.16	1.13	3.06	20.08	22.08	26.76	2.02	1.16	1.32	1.33	1.37
1780	6.39	7.42	7.51	7.13	1.12	3.21	20.29	22.33	27.15	1.98	1.15	1.31	1.32	1.36
1790	6.35	7.38	7.46	7.09	1.11	3.36	20.49	22.60	27.54	1.93	1.15	1.31	1.31	1.35
1800	6.32	7.34	7.42	7.05	1.10	3.50	20.69	22.94	27.89	1.89	1.14	1.29	1.30	1.34
1850	6.17	7.15	7.23	6.89	1.06	4.22	21.82	24.44	30.02	1.70	1.11	1.25	1.25	1.29
1860	6.15	7.12	7.20	6.86	1.05	2.48	22.04	24.76	30.39	1.67	1.11	1.25	1.25	1.29
1870	6.12	7.10	7.18	6.84	1.05	2.61	22.29	25.06	30.84	1.63	1.10	1.24	1.24	1.28
1880	6.10	7.06	7.15	6.81	1.05	4.62	22.53	25.43	31.19	1.60	1.10	1.23	1.23	1.27
1900	6.05	7.00	7.08	6.76	1.03	5.11	23.02	26.18	31.85	1.53	1.09	1.22	1.21	1.26
1930	6.00	6.92	7.00	6.70	1.00	5.81	23.81	27.41	32.46	1.44	1.07	1.19	1.19	1.24
1950	5.97	6.89	6.97	6.66	1.00	6.25	24.37	28.11	32.16	1.39	1.06	1.18	1.18	1.22
1960	5.96	6.86	6.94	6.65	0.98	6.49	24.58	28.55	32.03	1.36	1.06	1.17	1.17	1.22
1970	5.94	6.84	6.92	6.63	0.97	6.79	24.84	28.95	31.78	1.34	1.05	1.17	1.16	1.21
1980	5.94	6.85	6.93	6.62	0.99	7.17	25.11	29.30	31.58	1.32	1.05	1.17	1.15	1.20
1990	5.92	6.82	6.90	6.60	0.98	7.17	25.38	29.64	31.34	1.29	1.05	1.16	1.14	1.19
2000	5.91	6.79	6.88	6.59	0.97	7.39	25.68	30.06	30.96	1.27	1.04	1.16	1.14	1.19
2050	5.87	6.71	6.79	6.54	0.92	8.57	27.00	31.52	29.00	1.16	1.04	1.14	1.10	1.15
2060	5.87	6.69	6.78	6.53	0.91	8.82	27.29	31.73	28.64	1.14	1.04	1.13	1.10	1.15
2070	5.86	6.69	6.77	6.53	0.91	9.05	27.59	31.89	28.29	1.13	1.04	1.12	1.09	1.14
2080	5.86	6.68	6.76	6.52	0.90	9.26	27.75	31.91	27.94	1.11	1.04	1.12	1.09	1.14
2090	5.86	6.67	6.74	6.52	0.89	9.49	27.94	31.80	27.54	1.09	1.04	1.12	1.08	1.13
2100	5.85	6.66	6.74	6.51	0.89	9.79	28.19	31.74	27.21	1.08	1.05	1.11	1.08	1.12
2120	5.85	6.65	6.72	6.51	0.87	10.19	28.58	31.33	26.60	1.05	1.05	1.11	1.07	1.11
2160	5.84	6.63	6.70	6.52	0.86	11.17	29.06	29.98	25.44	1.06	1.07	1.11	1.06	1.09
2180	5.85	6.63	6.71	6.50	0.87	11.74	29.24	29.44	25.01	1.09	1.07	1.11	1.05	1.08
2200	5.85	6.63	6.71	6.51	0.86	12.06	29.36	28.80	24.44	1.12	1.08	1.11	1.05	1.07
2240	5.87	6.62	6.70	6.52	0.84	12.86	29.16	27.43	23.45	1.19	1.09	1.11	1.08	1.06
2260	5.88	6.63	6.70	6.53	0.83	13.33	28.95	26.78	23.02	1.22	1.10	1.11	1.09	1.06
2280	5.89	6.63	6.70	6.55	0.81	13.70	28.70	26.26	22.59	1.26	1.11	1.12	1.10	1.06
2320	5.92	6.64	6.72	6.58	0.80	14.53	28.10	25.11	21.87	1.32	1.13	1.14	1.12	1.05
2340	5.94	6.65	6.73	6.60	0.79	14.93	27.74	24.61	21.50	1.35	1.14	1.15	1.13	1.06
2380	5.97	6.69	6.77	6.63	0.79	15.70	27.05	23.60	20.99	1.43	1.15	1.16	1.16	1.06
2400	6.00	6.69	6.77	6.65	0.77	16.07	26.63	23.25	20.58	1.47	1.16	1.17	1.18	1.07
2440	6.04	6.72	6.80	6.71	0.76	16.88	25.89	22.34	20.03	1.54	1.17	1.20	1.21	1.08
2480	6.09	6.76	6.84	6.75	0.76	17.57	25.33	21.68	19.61	1.61	1.19	1.22	1.23	1.09
2500	6.11	6.78	6.86	6.78	0.75	18.02	24.99	21.36	19.37	1.65	1.20	1.23	1.24	1.10
2550	6.18	6.82	6.91	6.84	0.73	18.85	24.23	20.56	18.76	1.74	1.22	1.25	1.27	1.11
2600	6.26	6.88	6.97	6.93	0.71	19.78	23.56	19.87	18.25	1.84	1.24	1.28	1.32	1.13

¹Total Loss = Insertion Loss + 6dB Splitter Loss

REV. X2
BP4U+
100705
Page 2 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



4 Way-0° Power Splitter/Combiner

BP4U+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +85°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
1500	8.07	9.38	9.46	8.94	1.38	6.90	16.20	17.54	20.03	3.51	1.29	1.49	1.52	1.57
1550	7.72	8.99	9.06	8.56	1.34	5.69	16.84	18.25	21.00	3.11	1.26	1.45	1.48	1.52
1560	7.66	8.92	8.99	8.50	1.33	5.44	16.98	18.39	21.21	3.04	1.26	1.44	1.47	1.51
1570	7.59	8.85	8.92	8.43	1.32	5.24	17.12	18.55	21.43	2.96	1.25	1.44	1.46	1.50
1580	7.54	8.77	8.84	8.36	1.30	4.98	17.25	18.73	21.66	2.89	1.25	1.43	1.45	1.49
1590	7.47	8.71	8.77	8.29	1.30	4.74	17.40	18.89	21.89	2.83	1.24	1.42	1.44	1.48
1600	7.41	8.63	8.70	8.22	1.29	4.53	17.55	19.05	22.14	2.76	1.23	1.41	1.43	1.48
1650	7.14	8.32	8.39	7.93	1.25	3.67	18.35	19.98	23.47	2.46	1.20	1.38	1.38	1.43
1660	7.09	8.26	8.33	7.88	1.24	3.55	18.53	20.19	23.73	2.40	1.20	1.37	1.38	1.42
1670	7.04	8.21	8.28	7.83	1.24	3.45	18.70	20.39	24.05	2.35	1.19	1.36	1.37	1.41
1680	6.99	8.16	8.22	7.78	1.23	3.36	18.87	20.61	24.35	2.30	1.18	1.35	1.36	1.40
1690	6.95	8.10	8.17	7.73	1.22	3.25	19.05	20.82	24.67	2.25	1.18	1.35	1.34	1.40
1700	6.90	8.06	8.12	7.68	1.21	3.21	19.24	21.03	25.02	2.20	1.17	1.34	1.34	1.39
1750	6.70	7.82	7.87	7.46	1.17	2.78	20.22	22.26	26.85	1.98	1.14	1.30	1.30	1.35
1760	6.67	7.78	7.83	7.42	1.16	2.67	20.41	22.51	27.28	1.94	1.14	1.29	1.29	1.34
1770	6.64	7.74	7.79	7.39	1.15	2.59	20.62	22.80	27.64	1.90	1.13	1.28	1.28	1.33
1780	6.61	7.70	7.75	7.36	1.15	2.53	20.83	23.05	28.09	1.86	1.13	1.28	1.27	1.32
1790	6.58	7.66	7.71	7.32	1.13	2.42	21.05	23.35	28.51	1.82	1.12	1.27	1.27	1.31
1800	6.55	7.62	7.67	7.28	1.13	2.36	21.25	23.70	28.93	1.79	1.11	1.27	1.26	1.31
1850	6.42	7.46	7.50	7.14	1.09	2.93	22.45	25.29	31.19	1.62	1.09	1.24	1.22	1.27
1860	6.39	7.43	7.47	7.11	1.08	3.09	22.69	25.65	31.57	1.59	1.08	1.23	1.21	1.26
1870	6.37	7.40	7.45	7.09	1.08	3.21	22.95	26.02	31.95	1.56	1.08	1.22	1.21	1.25
1880	6.35	7.37	7.42	7.07	1.07	3.42	23.19	26.43	32.24	1.53	1.07	1.22	1.20	1.25
1900	6.31	7.32	7.37	7.02	1.06	3.86	23.73	27.27	32.79	1.48	1.06	1.21	1.18	1.23
1930	6.26	7.25	7.29	6.97	1.03	4.56	24.54	28.62	32.92	1.40	1.05	1.19	1.16	1.21
1950	6.24	7.21	7.26	6.93	1.03	4.93	25.10	29.33	32.34	1.35	1.04	1.19	1.15	1.20
1960	6.23	7.19	7.24	6.91	1.01	5.13	25.36	29.79	32.11	1.33	1.03	1.18	1.15	1.19
1970	6.22	7.18	7.22	6.90	1.00	5.47	25.60	30.32	31.92	1.31	1.03	1.17	1.14	1.19
1980	6.20	7.17	7.22	6.89	1.02	5.65	25.87	30.80	31.49	1.29	1.03	1.17	1.14	1.18
1990	6.19	7.15	7.20	6.87	1.01	5.82	26.16	31.05	31.24	1.27	1.03	1.17	1.13	1.17
2000	6.18	7.13	7.18	6.86	1.00	5.99	26.47	31.45	30.60	1.25	1.02	1.16	1.13	1.17
2050	6.16	7.05	7.10	6.82	0.94	5.46	27.73	32.65	28.64	1.16	1.02	1.15	1.11	1.14
2060	6.15	7.04	7.09	6.82	0.93	5.47	28.00	32.70	28.31	1.15	1.02	1.14	1.11	1.14
2070	6.15	7.03	7.08	6.81	0.93	5.69	28.24	32.73	27.92	1.13	1.02	1.14	1.10	1.13
2080	6.15	7.02	7.07	6.81	0.92	5.89	28.42	32.56	27.57	1.12	1.03	1.14	1.10	1.13
2090	6.15	7.02	7.06	6.80	0.91	7.95	28.56	32.36	27.26	1.11	1.03	1.14	1.10	1.12
2100	6.14	7.01	7.05	6.80	0.91	8.18	28.75	32.18	26.87	1.11	1.03	1.14	1.10	1.11
2120	6.15	7.00	7.04	6.80	0.89	8.61	29.03	31.55	26.31	1.10	1.04	1.13	1.10	1.11
2160	6.15	6.98	7.02	6.81	0.87	9.47	29.30	30.01	25.24	1.12	1.05	1.13	1.10	1.08
2180	6.15	6.98	7.03	6.80	0.88	9.95	29.30	29.19	24.80	1.13	1.06	1.13	1.10	1.08
2200	6.16	6.98	7.03	6.81	0.87	10.28	29.37	28.63	24.25	1.16	1.07	1.13	1.10	1.06
2240	6.18	6.97	7.03	6.83	0.84	11.00	28.93	27.25	23.32	1.21	1.08	1.13	1.11	1.05
2260	6.20	6.97	7.02	6.85	0.82	11.46	28.67	26.61	22.92	1.24	1.09	1.13	1.12	1.04
2280	6.22	6.99	7.03	6.86	0.81	11.82	28.35	26.11	22.53	1.27	1.10	1.13	1.13	1.04
2320	6.26	6.99	7.05	6.90	0.80	12.59	27.70	24.97	21.82	1.34	1.11	1.14	1.14	1.03
2340	6.28	7.00	7.06	6.92	0.78	12.99	27.35	24.50	21.48	1.37	1.12	1.14	1.15	1.03
2380	6.32	7.03	7.09	6.96	0.77	13.79	26.62	23.47	20.99	1.43	1.13	1.15	1.16	1.03
2400	6.34	7.04	7.10	6.98	0.75	14.03	26.28	23.19	20.60	1.47	1.14	1.15	1.16	1.03
2440	6.40	7.07	7.12	7.04	0.73	14.85	25.57	22.33	20.08	1.53	1.15	1.17	1.18	1.04
2480	6.45	7.11	7.17	7.09	0.72	15.52	25.09	21.68	19.68	1.60	1.16	1.17	1.19	1.06
2500	6.47	7.12	7.19	7.12	0.72	15.84	24.76	21.36	19.45	1.63	1.17	1.18	1.20	1.06
2550	6.55	7.16	7.23	7.18	0.68	16.68	24.08	20.61	18.86	1.72	1.18	1.20	1.22	1.08
2600	6.63	7.22	7.29	7.27	0.66	17.57	23.47	19.93	18.36	1.81	1.19	1.23	1.24	1.09

¹Total Loss = Insertion Loss + 6dB Splitter Loss

REV. X2
BP4U+
100705

Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see [minicircuits.com](http://www.minicircuits.com)