

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.5	99.63	0.00	120.0	11.32
1.0	97.13	0.00	123.0	29.24
2.0	91.12	0.00	125.0	34.39
5.0	73.38	0.00	126.0	34.58
8.0	65.14	0.02	127.0	33.24
10.0	61.28	0.00	128.0	31.01
20.0	49.44	0.00	130.0	25.94
30.0	42.26	0.01	132.0	21.87
40.0	37.12	0.01	134.0	19.26
50.0	33.05	0.03	136.0	17.62
60.0	29.58	0.05	138.0	16.70
70.0	26.52	0.09	139.0	16.33
80.0	23.80	0.13	140.0	16.08
90.0	21.44	0.19	141.0	15.94
100.0	19.73	0.30	142.0	15.86
130.0	1.43	18.05	144.0	15.80
140.0	1.00	21.87	146.0	16.10
150.0	1.19	26.10	148.0	16.38
160.0	4.42	4.71	150.0	17.58
170.0	16.60	0.83	152.0	18.68
180.0	33.50	0.38	154.0	20.32
190.0	24.41	0.28	155.0	21.10
200.0	22.86	0.24	158.0	22.76
260.0	27.22	0.20	160.0	22.53
300.0	31.50	0.22	163.0	20.07
350.0	36.85	0.24	165.0	17.22
400.0	41.93	0.26	167.0	14.27
450.0	46.94	0.29	168.0	12.82
500.0	51.40	0.30	169.0	11.67
600.0	58.09	0.33	170.0	9.98
650.0	58.70	0.34		
700.0	58.43	0.34		
750.0	57.72	0.34		
800.0	57.42	0.34		
850.0	56.81	0.35		
900.0	56.35	0.35		
950.0	56.13	0.34		
1000.0	55.49	0.35		
1050.0	55.67	0.34		
1100.0	55.50	0.32		
1150.0	55.92	0.32		
1200.0	55.97	0.32		
1250.0	55.86	0.30		
1300.0	55.22	0.29		
1350.0	54.44	0.29		
1400.0	53.37	0.29		
1450.0	51.74	0.29		
1500.0	49.95	0.28		
1600.0	43.27	0.28		
1700.0	38.19	0.29		
1750.0	37.06	0.29		
1800.0	36.92	0.30		
1900.0	34.55	0.33		
1950.0	32.97	0.35		
2000.0	30.96	0.47		