

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	81.19	0.00	300.0	34.19
10.0	85.42	0.00	302.0	26.57
50.0	71.31	0.01	305.0	31.40
100.0	55.54	0.02	308.0	19.36
150.0	47.63	0.04	310.0	15.19
200.0	44.99	0.10	312.0	15.48
250.0	49.79	0.21	315.0	17.62
300.0	47.39	0.53	319.0	24.83
309.0	40.69	0.74	320.0	28.65
314.0	29.01	1.02	322.0	37.54
320.0	15.91	2.16	325.0	50.49
329.0	4.56	14.27	329.0	42.72
330.0	4.48	13.60	330.0	40.89
332.0	4.43	14.17	332.0	39.14
335.0	4.65	22.44	332.2	39.38
340.0	7.52	9.46	332.5	39.50
350.0	28.16	2.17	332.7	39.39
350.5	29.37	2.14	333.0	39.64
360.0	47.07	1.97	333.2	39.65
370.0	38.43	2.10	333.5	39.88
380.0	34.33	1.95	333.7	40.04
390.0	33.48	1.64	334.0	40.23
400.0	34.11	1.38	334.2	40.61
410.0	35.45	1.21	334.5	41.11
420.0	37.26	1.13	334.7	40.87
430.0	39.36	1.05	335.0	41.30
440.0	42.03	0.98	335.5	42.19
450.0	45.34	0.93	336.0	42.99
460.0	49.63	0.88	336.5	43.52
470.0	56.52	0.81	337.0	44.01
480.0	69.96	0.73	337.2	44.62
490.0	57.35	0.71	337.5	45.32
500.0	52.88	0.66	337.7	45.35
550.0	46.70	0.56	338.0	46.08
600.0	46.39	0.54	338.5	46.66
650.0	47.44	0.57	339.0	46.55
700.0	49.09	0.58	339.2	46.98
750.0	51.26	0.56	339.5	47.06
800.0	54.03	0.53	339.7	46.53
850.0	57.54	0.50	340.0	46.58
900.0	61.89	0.48	341.0	45.02
950.0	73.15	0.44	342.0	42.21
1000.0	65.85	0.42	344.0	34.40
1050.0	57.03	0.41	345.0	30.54
1070.0	54.44	0.40	345.5	28.85
1080.0	52.87	0.39	346.0	27.18
1090.0	51.47	0.40	346.5	25.31
1120.0	46.23	0.40	347.0	23.58
1130.0	43.80	0.41	347.2	23.40
1150.0	38.44	0.45	347.5	22.46
1170.0	29.76	0.68	348.0	21.51
1180.0	23.07	1.36	349.0	19.03
1190.0	18.01	2.27	349.5	18.26
1200.0	18.67	1.25	350.0	17.04