

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.30	87.38	0.39	130.00	54.65
24.00	96.31	0.43	131.00	52.65
50.00	89.83	0.30	132.00	51.34
90.00	84.91	0.18	134.00	49.34
105.00	55.96	0.24	135.00	49.07
114.00	34.34	0.55	135.25	48.99
119.00	16.83	1.87	135.50	48.97
121.00	8.61	5.82	135.75	49.00
125.00	4.13	9.16	136.00	49.06
135.25	2.68	21.90	136.25	49.16
136.50	2.71	25.24	136.50	49.25
137.75	2.76	32.41	136.75	49.40
144.00	4.16	18.85	137.00	49.33
147.00	9.14	5.22	137.25	49.51
152.00	21.62	1.69	137.50	49.60
160.00	36.19	0.83	137.75	49.78
176.00	53.89	0.42	138.00	49.81
230.00	85.85	0.17	138.25	50.10
255.00	100.33	0.13	138.50	50.29
665.00	87.40	0.15	139.00	50.60
765.00	101.41	0.19	139.25	50.90
800.00	94.04	0.19	139.50	51.35
900.00	88.33	0.20	139.75	52.21
1000.00	90.97	0.20	140.00	53.24