

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	87.52	0.04	95.0	121.68
10.0	72.92	0.04	95.2	117.55
20.0	66.92	0.03	95.4	113.74
50.0	57.39	0.06	96.0	104.27
65.0	53.93	0.09	96.6	97.73
70.0	52.86	0.11	97.0	94.75
88.0	61.47	0.90	97.2	93.55
90.6	31.01	2.22	97.8	90.97
91.8	19.82	4.38	98.0	90.31
95.0	5.71	16.47	98.2	89.72
98.0	4.57	13.64	98.4	89.22
101.0	5.21	10.50	98.6	88.72
106.0	20.77	3.70	98.8	88.28
107.2	30.77	2.08	99.0	87.92
108.0	38.20	1.55	99.2	87.56
120.0	75.35	0.24	99.4	87.34
250.0	71.25	0.07	99.6	87.22
450.0	77.29	0.05	99.8	87.20
700.0	54.70	0.04	100.0	87.35
900.0	48.51	0.02	100.2	87.65
1200.0	45.72	0.01	100.4	88.23
1500.0	41.21	0.03	100.6	88.99
1750.0	37.41	0.07	100.8	89.98
2000.0	33.02	0.14	101.0	91.27