

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
2400	0.64	10.60	17.64	15.72	15.87	18.49
2402	0.65	10.59	17.66	15.72	15.85	18.49
2405	0.65	10.59	17.67	15.74	15.87	18.48
2408	0.65	10.57	17.70	15.73	15.87	18.48
2411	0.65	10.57	17.72	15.73	15.87	18.48
2414	0.65	10.56	17.73	15.74	15.88	18.46
2417	0.65	10.55	17.75	15.74	15.89	18.47
2420	0.65	10.54	17.78	15.75	15.90	18.46
2423	0.65	10.53	17.80	15.76	15.90	18.47
2426	0.65	10.53	17.83	15.76	15.90	18.47
2429	0.65	10.51	17.88	15.75	15.90	18.48
2432	0.66	10.51	17.88	15.77	15.90	18.46
2435	0.66	10.50	17.91	15.77	15.92	18.46
2438	0.66	10.49	17.93	15.77	15.94	18.47
2441	0.66	10.48	17.95	15.79	15.94	18.45
2444	0.66	10.48	18.00	15.78	15.95	18.46
2447	0.66	10.47	18.02	15.79	15.95	18.48
2450	0.66	10.46	18.02	15.79	15.97	18.46
2452	0.66	10.45	18.04	15.79	15.98	18.46
2455	0.66	10.45	18.08	15.79	15.99	18.44
2458	0.66	10.44	18.11	15.79	16.00	18.45
2461	0.67	10.43	18.11	15.80	16.01	18.45
2464	0.67	10.42	18.16	15.81	16.01	18.47
2467	0.67	10.41	18.16	15.82	16.02	18.44
2470	0.67	10.40	18.20	15.82	16.01	18.45
2473	0.67	10.40	18.23	15.82	16.04	18.44
2476	0.67	10.39	18.24	15.83	16.04	18.44
2479	0.67	10.38	18.29	15.84	16.06	18.44
2482	0.67	10.37	18.31	15.83	16.05	18.44
2485	0.67	10.36	18.32	15.86	16.06	18.43
2488	0.67	10.35	18.35	15.85	16.08	18.44
2491	0.67	10.34	18.38	15.85	16.07	18.42
2494	0.68	10.34	18.40	15.84	16.09	18.42
2497	0.68	10.32	18.43	15.85	16.09	18.41
2500	0.68	10.32	18.43	15.85	16.10	18.40