

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT VSWR (:1)	OUTPUT VSWR (:1)
500	29.47	318.52	627.16
600	28.03	418.60	901.45
700	26.86	373.48	759.22
800	25.87	490.06	493.31
900	25.09	406.88	1424.62
1000	24.45	409.85	604.01
1200	23.61	231.92	4581.17
1400	23.25	161.03	1137.05
1600	23.43	130.54	1184.66
1800	24.31	112.21	301.69
2000	26.30	97.90	298.54
2200	30.86	83.16	199.18
2400	43.28	73.96	122.82
2410	42.65	74.27	121.84
2420	41.32	73.48	121.42
2430	40.30	72.56	121.57
2440	38.89	71.89	123.66
2450	37.90	70.65	123.11
2460	36.59	70.48	122.49
2470	35.78	69.89	119.59
2480	34.64	69.92	115.57
2490	33.94	69.33	111.14
2500	32.96	68.39	109.17
2600	26.86	61.60	95.60
2700	22.71	52.55	76.12
2800	19.47	43.66	55.70
2900	16.71	35.89	43.44
3000	14.28	28.09	31.83
3100	12.08	21.74	23.52
3200	10.06	16.24	17.26
3300	8.19	12.03	12.43
3400	6.52	8.72	8.79
3500	5.03	6.30	6.25
3600	3.78	4.57	4.49
3700	2.78	3.39	3.30
3800	2.00	2.58	2.50
3900	1.46	2.05	1.96
4000	1.10	1.69	1.60
4100	0.87	1.45	1.35
4200	0.73	1.31	1.19
4300	0.64	1.22	1.10
4400	0.58	1.19	1.08
4500	0.54	1.18	1.10
4600	0.51	1.17	1.12
4700	0.49	1.16	1.14
4800	0.46	1.14	1.13
4900	0.44	1.12	1.12
5000	0.43	1.09	1.12
5100	0.41	1.07	1.11
5200	0.40	1.07	1.12
5300	0.40	1.09	1.15
5400	0.39	1.13	1.18
5500	0.40	1.17	1.22
5600	0.41	1.21	1.26
5700	0.42	1.25	1.30
5800	0.43	1.29	1.33
5850	0.43	1.31	1.35
5900	0.44	1.32	1.36
6000	0.44	1.35	1.39
6200	0.45	1.38	1.42
6400	0.45	1.38	1.40
6600	0.44	1.33	1.36
6800	0.41	1.27	1.28
7000	0.40	1.18	1.18
7200	0.39	1.10	1.08
7400	0.40	1.08	1.02
7600	0.43	1.14	1.12
7800	0.48	1.23	1.23
8000	0.54	1.30	1.31