

Frequency Mixer

JMS-2L

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)		
		@LO (dBm)		
		0	+3	+6
800.1	830.1	7.20	6.27	5.72
818.0	848.0	7.36	6.45	5.83
836.0	866.0	7.47	6.54	5.93
853.9	883.9	7.60	6.70	6.09
871.9	901.9	7.75	6.83	6.20
889.8	919.8	7.79	6.90	6.27
907.8	937.8	7.95	7.10	6.48
925.7	955.7	8.09	7.24	6.62
943.7	973.7	8.20	7.41	6.79
961.6	991.6	8.34	7.55	6.97
979.6	1009.6	8.35	7.62	7.07
997.5	1027.5	8.46	7.75	7.26
1015.5	1045.5	8.53	7.82	7.35
1033.4	1063.4	8.56	7.89	7.48
1051.4	1081.4	8.68	7.93	7.55
1069.3	1099.3	8.67	7.93	7.57
1087.3	1117.3	8.77	7.95	7.61
1105.2	1135.2	8.94	8.03	7.69
1123.2	1153.2	8.95	8.05	7.70
1141.1	1171.1	9.19	8.15	7.74
1159.1	1189.1	9.25	8.20	7.80
1177.0	1207.0	9.40	8.29	7.88
1195.0	1225.0	9.57	8.38	7.92
1212.9	1242.9	9.55	8.38	7.95
1230.9	1260.9	9.86	8.51	8.03
1248.8	1278.8	9.93	8.55	8.06
1266.8	1296.8	10.02	8.62	8.06
1284.7	1314.7	10.23	8.70	8.13
1302.7	1332.7	10.20	8.69	8.16
1320.6	1350.6	10.52	8.84	8.17
1338.6	1368.6	10.67	8.88	8.23
1356.5	1386.5	10.74	8.92	8.25
1374.5	1404.5	11.05	9.03	8.29
1392.4	1422.4	11.04	9.06	8.29
1410.4	1440.4	11.36	9.20	8.40
1428.3	1458.3	11.62	9.32	8.44
1446.3	1476.3	11.63	9.33	8.44
1464.2	1494.2	12.13	9.56	8.53
1482.2	1512.2	12.15	9.59	8.58
1500.1	1530.1	12.55	9.76	8.65

RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)		
		@LO (dBm)		
		0	+3	+6
800.1	830.1	13.41	13.73	12.98
818.0	848.0	11.05	13.51	14.89
836.0	866.0	11.02	13.33	13.85
853.9	883.9	10.51	10.77	12.96
871.9	901.9	9.31	12.15	13.91
889.8	919.8	8.22	11.18	13.29
907.8	937.8	8.41	11.96	14.50
925.7	955.7	8.80	9.60	12.38
943.7	973.7	9.80	9.86	11.52
961.6	991.6	7.67	9.37	9.66
979.6	1009.6	8.88	9.23	10.20
997.5	1027.5	7.66	8.64	9.96
1015.5	1045.5	7.78	9.56	11.63
1033.4	1063.4	8.77	8.25	9.62
1051.4	1081.4	8.18	8.86	8.99
1069.3	1099.3	8.33	9.30	10.44
1087.3	1117.3	8.97	9.03	7.79
1105.2	1135.2	9.28	8.68	8.02
1123.2	1153.2	9.83	9.65	9.49
1141.1	1171.1	9.89	10.44	9.95
1159.1	1189.1	8.79	10.98	9.48
1177.0	1207.0	9.13	9.57	8.66
1195.0	1225.0	9.03	9.99	8.93
1212.9	1242.9	8.69	10.13	10.47
1230.9	1260.9	9.08	9.61	8.58
1248.8	1278.8	9.45	8.85	10.24
1266.8	1296.8	9.93	9.83	10.79
1284.7	1314.7	9.02	9.37	11.09
1302.7	1332.7	8.36	9.25	10.78
1320.6	1350.6	9.24	9.01	10.57
1338.6	1368.6	11.95	9.58	8.60
1356.5	1386.5	9.68	8.24	11.35
1374.5	1404.5	12.02	8.03	10.08
1392.4	1422.4	11.56	7.98	11.19
1410.4	1440.4	12.39	9.49	9.97
1428.3	1458.3	12.01	7.59	8.08
1446.3	1476.3	9.68	7.65	8.95
1464.2	1494.2	10.96	7.73	8.68
1482.2	1512.2	7.89	7.92	8.54
1500.1	1530.1	8.62	7.65	9.23

RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=-3dBm (dB)		
		@LO (dBm)		
		0	+3	+6
800.1	830.1	1.24	0.62	0.49
818.0	848.0	1.20	0.71	0.56
836.0	866.0	1.12	0.68	0.56
853.9	883.9	1.04	0.63	0.55
871.9	901.9	0.98	0.60	0.52
889.8	919.8	0.90	0.54	0.49
907.8	937.8	0.88	0.53	0.47
925.7	955.7	0.81	0.48	0.43
943.7	973.7	0.77	0.43	0.39
961.6	991.6	0.73	0.39	0.34
979.6	1009.6	0.66	0.34	0.32
997.5	1027.5	0.64	0.30	0.27
1015.5	1045.5	0.65	0.30	0.24
1033.4	1063.4	0.58	0.28	0.16
1051.4	1081.4	0.63	0.27	0.15
1069.3	1099.3	0.59	0.27	0.15
1087.3	1117.3	0.59	0.25	0.15
1105.2	1135.2	0.58	0.28	0.16
1123.2	1153.2	0.55	0.29	0.15
1141.1	1171.1	0.55	0.30	0.17
1159.1	1189.1	0.53	0.26	0.17
1177.0	1207.0	0.52	0.29	0.16
1195.0	1225.0	0.53	0.30	0.16
1212.9	1242.9	0.50	0.30	0.17
1230.9	1260.9	0.52	0.33	0.19
1248.8	1278.8	0.53	0.33	0.19
1266.8	1296.8	0.48	0.34	0.20
1284.7	1314.7	0.52	0.37	0.23
1302.7	1332.7	0.49	0.37	0.24
1320.6	1350.6	0.47	0.40	0.25
1338.6	1368.6	0.49	0.39	0.24
1356.5	1386.5	0.45	0.41	0.25
1374.5	1404.5	0.42	0.42	0.27
1392.4	1422.4	0.39	0.42	0.28
1410.4	1440.4	0.36	0.43	0.29
1428.3	1458.3	0.30	0.45	0.30
1446.3	1476.3	0.31	0.47	0.29
1464.2	1494.2	0.20	0.44	0.35
1482.2	1512.2	0.23	0.45	0.35
1500.1	1530.1	0.16	0.44	0.36

REV. X2

JMS-2L

100817

Page 1 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Frequency Mixer

JMS-2L

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=900.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=800.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=1000.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+3			+3			+3
100.0	800.1	7.04	10.0	810.1	6.69	200.0	800.1	7.66
95.3	804.8	7.11	14.9	815.0	6.50	195.1	805.0	7.71
90.5	809.6	7.12	19.7	819.8	6.41	190.3	809.8	7.73
85.8	814.3	7.12	24.6	824.7	6.33	185.4	814.7	7.70
81.1	819.0	7.11	29.5	829.6	6.30	180.5	819.6	7.72
76.3	823.8	7.11	34.3	834.4	6.25	175.6	824.5	7.72
71.6	828.5	7.09	39.2	839.3	6.24	170.8	829.3	7.74
66.8	833.3	7.10	44.1	844.2	6.33	165.9	834.2	7.76
62.1	838.0	7.12	49.0	849.1	6.36	161.0	839.1	7.80
57.4	842.7	7.12	53.8	853.9	6.32	156.2	843.9	7.86
52.6	847.5	7.14	58.7	858.8	6.32	151.3	848.8	7.87
47.9	852.2	7.12	63.6	863.7	6.32	146.4	853.7	7.88
43.2	856.9	7.11	68.4	868.5	6.27	141.5	858.6	7.87
38.4	861.7	7.09	73.3	873.4	6.30	136.7	863.4	7.83
33.7	866.4	7.11	78.2	878.3	6.29	131.8	868.3	7.82
28.9	871.2	7.14	83.0	883.1	6.25	126.9	873.2	7.84
24.2	875.9	7.13	87.9	888.0	6.26	122.1	878.0	7.80
19.5	880.6	7.14	92.8	892.9	6.25	117.2	882.9	7.83
14.7	885.4	7.14	97.6	897.7	6.27	112.3	887.8	7.82
10.0	890.1	7.19	102.5	902.6	6.26	107.4	892.7	7.83
10.0	910.1	7.20	107.4	907.5	6.24	102.6	897.5	7.83
14.5	914.6	7.14	112.3	912.4	6.22	97.7	902.4	7.83
19.0	919.1	7.08	117.1	917.2	6.23	92.8	907.3	7.80
23.5	923.6	7.05	122.0	922.1	6.20	87.9	912.2	7.79
28.0	928.1	7.06	126.9	927.0	6.24	83.1	917.0	7.75
32.5	932.6	7.06	131.7	931.8	6.24	78.2	921.9	7.81
37.0	937.1	7.05	136.6	936.7	6.28	73.3	926.8	7.82
41.5	941.6	7.07	141.5	941.6	6.32	68.5	931.6	7.80
46.0	946.1	7.07	146.3	946.4	6.32	63.6	936.5	7.81
50.5	950.6	7.07	151.2	951.3	6.34	58.7	941.4	7.80
55.0	955.1	7.05	156.1	956.2	6.35	53.8	946.3	7.81
59.5	959.6	7.05	160.9	961.0	6.30	49.0	951.1	7.83
64.0	964.1	7.04	165.8	965.9	6.31	44.1	956.0	7.78
68.5	968.6	7.04	170.7	970.8	6.33	39.2	960.9	7.71
73.0	973.1	7.07	175.6	975.7	6.33	34.4	965.7	7.73
77.5	977.6	7.08	180.4	980.5	6.35	29.5	970.6	7.71
82.0	982.1	7.09	185.3	985.4	6.36	24.6	975.5	7.81
86.5	986.6	7.09	190.2	990.3	6.39	19.7	980.4	7.93
95.5	995.6	7.09	195.0	995.1	6.37	14.9	985.2	7.98
100.0	1000.1	7.09	199.9	1000.0	6.36	10.0	990.1	7.80

REV. X2

JMS-2L

100817

Page 2 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	0	+3	+6	0	+3	+6
800.1	30.43	32.11	31.58	24.66	23.00	20.84
818.0	29.16	30.66	30.37	24.20	22.22	20.08
836.0	28.07	29.39	29.30	23.68	21.50	19.38
853.9	27.03	28.32	28.47	23.34	21.17	18.99
871.9	26.20	27.37	27.59	22.93	20.61	18.43
889.8	25.36	26.46	26.78	22.36	20.14	17.96
907.8	24.70	25.74	26.07	21.81	19.61	17.43
925.7	24.17	25.15	25.52	21.39	19.19	17.06
943.7	23.58	24.53	24.96	21.01	19.01	16.91
961.6	23.13	24.03	24.44	20.49	18.52	16.50
979.6	22.65	23.53	23.98	20.12	18.32	16.35
997.5	22.28	23.13	23.58	19.66	17.97	16.08
1015.5	21.96	22.76	23.17	19.06	17.43	15.62
1033.4	21.59	22.41	22.85	18.72	17.29	15.56
1051.4	21.37	22.20	22.64	18.36	17.01	15.36
1069.3	21.08	21.90	22.32	17.90	16.70	15.15
1087.3	20.77	21.62	22.05	17.37	16.32	14.86
1105.2	20.59	21.45	21.88	16.94	15.93	14.53
1123.2	20.34	21.23	21.69	16.53	15.65	14.37
1141.1	20.11	21.03	21.52	16.09	15.29	14.04
1159.1	19.95	20.89	21.40	15.69	14.98	13.82
1177.0	19.73	20.72	21.27	15.30	14.70	13.62
1195.0	19.61	20.59	21.14	14.85	14.26	13.22
1212.9	19.40	20.42	21.02	14.50	14.02	13.07
1230.9	19.34	20.40	21.03	14.16	13.72	12.80
1248.8	19.24	20.31	20.95	13.77	13.37	12.51
1266.8	18.98	20.12	20.83	13.41	13.11	12.37
1284.7	19.04	20.20	20.93	13.12	12.81	12.09
1302.7	18.88	20.08	20.84	12.74	12.52	11.87
1320.6	18.74	19.99	20.79	12.38	12.20	11.59
1338.6	18.72	20.00	20.85	12.14	12.00	11.43
1356.5	18.59	19.95	20.88	11.84	11.80	11.31
1374.5	18.56	19.93	20.88	11.50	11.47	11.00
1392.4	18.39	19.81	20.81	11.19	11.25	10.84
1410.4	18.31	19.78	20.86	10.95	11.08	10.71
1428.3	18.32	19.78	20.89	10.69	10.84	10.51
1446.3	18.13	19.65	20.83	10.37	10.62	10.37
1464.2	18.13	19.66	20.87	10.13	10.45	10.24
1482.2	18.06	19.58	20.83	9.83	10.21	10.06
1500.1	17.90	19.42	20.70	9.57	10.02	9.95

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		0	+3	+6
800.1	830.1	18.56	17.36	15.91
818.0	848.0	17.80	16.96	15.79
836.0	866.0	17.05	16.44	15.49
853.9	883.9	16.28	15.83	15.13
871.9	901.9	15.62	15.29	14.77
889.8	919.8	14.99	14.76	14.36
907.8	937.8	14.47	14.32	14.08
925.7	955.7	14.01	13.90	13.74
943.7	973.7	13.55	13.47	13.37
961.6	991.6	13.20	13.15	13.10
979.6	1009.6	12.82	12.78	12.73
997.5	1027.5	12.51	12.48	12.48
1015.5	1045.5	12.21	12.22	12.23
1033.4	1063.4	11.98	11.98	12.00
1051.4	1081.4	11.79	11.84	11.89
1069.3	1099.3	11.60	11.67	11.74
1087.3	1117.3	11.41	11.52	11.64
1105.2	1135.2	11.24	11.41	11.55
1123.2	1153.2	11.11	11.31	11.50
1141.1	1171.1	10.95	11.22	11.43
1159.1	1189.1	10.86	11.17	11.42
1177.0	1207.0	10.75	11.11	11.39
1195.0	1225.0	10.68	11.11	11.41
1212.9	1242.9	10.65	11.12	11.44
1230.9	1260.9	10.55	11.09	11.44
1248.8	1278.8	10.53	11.14	11.52
1266.8	1296.8	10.50	11.17	11.57
1284.7	1314.7	10.45	11.21	11.65
1302.7	1332.7	10.50	11.30	11.77
1320.6	1350.6	10.38	11.31	11.83
1338.6	1368.6	10.40	11.41	11.97
1356.5	1386.5	10.42	11.50	12.10
1374.5	1404.5	10.32	11.53	12.21
1392.4	1422.4	10.41	11.68	12.39
1410.4	1440.4	10.30	11.69	12.49
1428.3	1458.3	10.29	11.79	12.65
1446.3	1476.3	10.31	11.86	12.76
1464.2	1494.2	10.16	11.83	12.84
1482.2	1512.2	10.23	11.94	13.00
1500.1	1530.1	10.01	11.80	12.96

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)			LO (MHz)	LO VSWR (:1)			IF (OUT) (MHz)	IF VSWR @LO=1000.1MHz (:1)		
		@LO (dBm)				@LO (dBm)				@LO (dBm)		
		0	+3	+6		0	+3	+6		0	+3	+6
800.1	830.1	2.24	2.02	1.88	800.1	1.68	2.14	2.69	10.0	3.34	2.37	2.03
818.0	848.0	2.45	2.23	2.09	818.0	1.72	2.19	2.76	14.9	2.72	2.31	1.70
836.0	866.0	2.67	2.44	2.28	836.0	1.76	2.23	2.79	19.7	2.66	2.39	1.97
853.9	883.9	2.80	2.57	2.40	853.9	1.76	2.21	2.74	24.6	2.65	2.16	1.81
871.9	901.9	2.84	2.61	2.45	871.9	1.79	2.24	2.77	29.5	2.49	2.32	1.63
889.8	919.8	2.90	2.71	2.55	889.8	1.81	2.24	2.75	34.4	2.46	1.96	1.54
907.8	937.8	3.14	2.96	2.81	907.8	1.86	2.30	2.82	39.2	2.45	2.00	1.62
925.7	955.7	3.34	3.16	3.01	925.7	1.92	2.36	2.89	44.1	2.26	1.90	1.58
943.7	973.7	3.35	3.19	3.05	943.7	1.93	2.35	2.86	49.0	2.24	1.82	1.50
961.6	991.6	3.28	3.14	3.03	961.6	1.97	2.39	2.89	53.8	2.13	1.83	1.50
979.6	1009.6	3.30	3.20	3.12	979.6	1.98	2.37	2.86	58.7	2.16	1.78	1.51
997.5	1027.5	3.48	3.40	3.34	997.5	2.01	2.40	2.89	63.6	2.19	1.72	1.39
1015.5	1045.5	3.61	3.52	3.49	1015.5	2.07	2.48	2.98	68.5	2.16	1.81	1.46
1033.4	1063.4	3.52	3.43	3.42	1033.4	2.11	2.49	2.97	73.3	2.15	1.81	1.44
1051.4	1081.4	3.42	3.33	3.33	1051.4	2.15	2.52	3.00	78.2	2.22	1.84	1.51
1069.3	1099.3	3.52	3.43	3.44	1069.3	2.17	2.52	2.97	83.1	2.25	1.87	1.52
1087.3	1117.3	3.72	3.60	3.62	1087.3	2.18	2.52	2.96	87.9	2.26	1.87	1.62
1105.2	1135.2	3.86	3.70	3.70	1105.2	2.25	2.59	3.04	92.8	2.31	1.92	1.61
1123.2	1153.2	3.79	3.61	3.60	1123.2	2.30	2.63	3.06	97.7	2.39	1.92	1.65
1141.1	1171.1	3.76	3.56	3.55	1141.1	2.36	2.67	3.11	102.6	2.40	1.97	1.66
1159.1	1189.1	3.93	3.73	3.72	1159.1	2.40	2.69	3.10	107.4	2.39	2.04	1.66
1177.0	1207.0	4.16	3.94	3.90	1177.0	2.41	2.67	3.07	112.3	2.40	1.96	1.66
1195.0	1225.0	4.28	4.01	3.96	1195.0	2.46	2.73	3.12	117.2	2.44	1.98	1.65
1212.9	1242.9	4.14	3.90	3.85	1212.9	2.51	2.75	3.13	122.1	2.48	2.01	1.66
1230.9	1260.9	4.14	3.88	3.83	1230.9	2.58	2.82	3.19	126.9	2.44	1.95	1.66
1248.8	1278.8	4.29	4.02	3.96	1248.8	2.63	2.86	3.21	131.8	2.40	1.98	1.67
1266.8	1296.8	4.46	4.18	4.09	1266.8	2.65	2.83	3.16	136.7	2.36	1.93	1.62
1284.7	1314.7	4.51	4.18	4.08	1284.7	2.69	2.87	3.19	141.5	2.30	1.92	1.65
1302.7	1332.7	4.37	4.06	3.95	1302.7	2.73	2.89	3.19	146.4	2.29	1.92	1.59
1320.6	1350.6	4.36	4.03	3.91	1320.6	2.81	2.94	3.26	151.3	2.25	1.88	1.59
1338.6	1368.6	4.39	4.07	3.96	1338.6	2.87	3.00	3.29	156.2	2.28	1.87	1.58
1356.5	1386.5	4.60	4.22	4.06	1356.5	2.92	3.00	3.25	161.0	2.20	1.87	1.58
1374.5	1404.5	4.55	4.13	3.96	1374.5	2.93	3.00	3.24	165.9	2.26	1.88	1.59
1392.4	1422.4	4.42	4.03	3.86	1392.4	2.98	3.03	3.25	170.8	2.22	1.87	1.59
1410.4	1440.4	4.53	4.11	3.92	1410.4	3.04	3.08	3.29	175.6	2.33	1.89	1.63
1428.3	1458.3	4.79	4.33	4.10	1428.3	3.10	3.14	3.33	180.5	2.29	1.94	1.64
1446.3	1476.3	4.75	4.27	4.03	1446.3	3.18	3.17	3.32	185.4	2.33	1.96	1.66
1464.2	1494.2	4.74	4.22	3.96	1464.2	3.20	3.18	3.33	190.3	2.36	1.99	1.65
1482.2	1512.2	4.74	4.22	3.95	1482.2	3.22	3.19	3.31	195.1	2.40	1.99	1.67
1500.1	1530.1	4.92	4.36	4.06	1500.1	3.26	3.20	3.30	200.0	2.38	1.96	1.68

Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	+9	4	6	27	30	47	45	55	60	68
1	-	7	+0	21	24	31	48	45	58	56	65	69
2	115	42	39	41	37	49	52	56	74	71	73	71
3	122	67	62	57	84	61	73	67	87	76	87	85
4	114	98	89	95	85	75	99	90	101	101	99	92
5	118	94	109	99	98	90	75	97	97	94	99	103
6	113	111	95	98	104	100	101	87	90	91	100	104
7	107	95	105	106	99	95	90	87	77	96	90	90
8	110	97	114	106	98	106	103	91	91	84	97	96
9	113	97	96	105	108	100	97	97	94	98	82	92
10	115	100	95	96	112	96	103	96	107	97	109	83
RF CAL	0	1	2	3	4	5	6	7	8	9	10	

LO HARMONICS ORDER

Test conditions:

RF IN: 900.1 MHz; -18.00 dBm.

LO IN: 930.01 MHz; +3.00 dBm

IF OUT: 29.91 MHz; -25.19 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	1	15	18	41	41	70	66	69	78	82
1	-	7	+0	22	25	33	52	53	66	67	77	87
2	100	32	30	34	28	41	43	51	64	69	77	80
3	122	46	42	38	58	44	56	51	67	64	74	76
4	112	70	66	61	57	51	62	59	69	70	77	81
5	123	85	74	76	79	62	79	64	73	68	92	81
6	109	104	95	91	85	83	78	72	84	79	81	100
7	113	104	103	109	103	103	85	80	80	84	90	86
8	100	99	109	105	114	103	106	92	88	90	92	99
9	117	111	100	109	108	107	111	103	100	102	92	93
10	111	104	107	106	102	110	110	109	117	112	96	98
RF CAL	0	1	2	3	4	5	6	7	8	9	10	

LO HARMONICS ORDER

Test conditions:

RF IN: 900.1 MHz; -8.00 dBm.

LO IN: 930.01 MHz; +3.00 dBm

IF OUT: 29.91 MHz; -15.23 dBm

Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.

2. + entry denotes harmonics are in (dBc) above IF OUTPUT.

3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2

JMS-2L

100817

Page 5 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see

