

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100	0.06	43.7	43.6
200	0.08	44.1	43.3
300	0.10	42.1	41.7
400	0.11	39.0	39.0
500	0.12	38.2	38.0
600	0.13	41.5	40.3
700	0.14	50.6	44.1
800	0.16	38.2	37.8
900	0.17	34.2	34.2
1000	0.17	34.0	34.1
1100	0.18	38.2	38.4
1250	0.19	40.5	39.8
1500	0.21	31.9	32.1
1750	0.23	39.0	38.5
2000	0.24	31.8	32.2
2250	0.25	36.5	36.1
2500	0.27	32.4	33.0
2750	0.28	34.9	34.6
3000	0.29	34.5	35.7
3250	0.30	33.2	32.9
3500	0.31	38.0	40.3
3750	0.33	31.5	31.1
4000	0.33	37.8	39.3
4250	0.35	30.6	30.2
4500	0.36	33.5	33.8
5000	0.38	30.7	30.8
5500	0.39	28.6	28.7
6000	0.41	27.1	27.2
6500	0.43	26.4	26.5
7000	0.45	26.2	26.4
7500	0.46	26.9	27.1
8000	0.47	27.6	28.0
8500	0.48	28.9	29.5
9000	0.49	31.3	32.1
9500	0.51	34.5	34.8
10000	0.52	39.5	41.7
10500	0.53	42.0	44.8
11000	0.54	39.3	42.5
11500	0.56	38.6	40.4
12000	0.57	37.9	38.2
12500	0.58	40.9	43.5
13000	0.59	45.4	54.7
13500	0.61	37.6	37.0
14000	0.62	33.1	32.5
14500	0.64	29.0	28.5
15000	0.65	26.3	25.8
15500	0.67	24.7	24.2
16000	0.69	23.3	22.8
16500	0.70	22.9	22.4
17000	0.72	22.6	22.1
17500	0.72	23.2	22.6
18000	0.73	24.1	23.5