

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100	0.03	39.4	39.3
200	0.05	34.0	33.9
300	0.06	32.7	32.7
400	0.07	34.5	34.5
500	0.08	41.9	41.6
600	0.09	42.1	41.8
700	0.09	33.9	33.7
800	0.10	31.4	31.2
900	0.11	32.4	32.3
1000	0.11	38.9	38.4
1100	0.11	42.8	41.5
1250	0.13	30.9	31.0
1500	0.13	38.6	37.5
1750	0.14	30.3	30.4
2000	0.15	38.8	36.8
2250	0.16	29.2	28.9
2500	0.16	40.5	38.0
2750	0.18	27.6	27.7
3000	0.17	43.3	41.7
3250	0.18	27.2	27.6
3500	0.18	38.8	42.5
3750	0.19	28.4	26.7
4000	0.19	35.6	34.9
4250	0.20	27.7	26.8
4500	0.21	31.2	31.2
5000	0.23	28.0	28.3
5500	0.25	26.2	26.1
6000	0.26	24.8	24.9
6500	0.28	24.0	24.3
7000	0.28	23.8	24.1
7500	0.30	23.7	23.6
8000	0.30	24.4	25.1
8500	0.30	25.6	25.8
9000	0.30	27.0	27.3
9500	0.31	29.9	30.4
10000	0.32	33.5	35.0
10500	0.32	39.3	41.9
11000	0.33	39.2	40.6
11500	0.34	32.4	30.3
12000	0.34	31.0	29.5
12500	0.36	30.4	28.3
13000	0.36	30.0	27.9
13500	0.37	31.3	29.4
14000	0.37	31.9	30.2
14500	0.38	34.2	31.4
15000	0.38	34.4	30.1
15500	0.39	31.6	29.9
16000	0.40	29.8	29.6
16500	0.41	26.6	28.1
17000	0.42	26.3	25.9
17500	0.42	26.6	29.2
18000	0.43	25.4	26.1