

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	
		50-Ohm	75-Ohm
0.3	0.71	16.03	15.05
0.4	0.63	18.15	16.50
0.5	0.59	19.71	17.46
0.6	0.55	20.96	18.11
0.7	0.53	21.94	18.58
0.8	0.51	22.75	19.00
0.9	0.49	23.49	19.35
1.0	0.47	24.09	19.61
2.0	0.38	28.05	21.40
3.0	0.33	30.30	22.26
4.0	0.30	31.89	22.84
5.0	0.29	33.09	23.30
6.0	0.29	33.94	23.52
7.0	0.28	34.63	23.74
8.0	0.28	35.18	23.86
9.0	0.28	35.58	23.95
10	0.27	35.96	23.98
20	0.28	37.35	24.20
30	0.28	37.76	24.27
40	0.29	38.06	24.17
50	0.30	38.15	24.08
60	0.31	38.12	23.95
70	0.31	38.06	23.81
80	0.32	37.86	23.70
90	0.32	37.60	23.65
100	0.32	37.44	23.61
150	0.33	36.17	24.17
200	0.37	34.72	25.16
250	0.38	33.71	25.11
300	0.40	32.87	24.63
350	0.40	31.85	23.63
400	0.43	31.09	22.97
450	0.44	30.55	23.40
500	0.45	29.78	23.61
550	0.47	29.31	23.55
600	0.49	29.27	24.34
650	0.50	29.08	25.10
700	0.52	28.84	24.83
750	0.53	29.06	24.95
800	0.55	29.10	24.80
850	0.57	28.83	23.98
900	0.59	28.83	23.80
950	0.60	28.92	24.60
1000	0.62	28.66	24.77
1050	0.64	28.77	24.63
1100	0.67	29.05	26.12
1150	0.70	28.91	25.98
1200	0.72	28.94	25.15
1250	0.73	29.46	26.41
1300	0.76	29.55	27.88
1350	0.78	29.24	29.05
1400	0.80	29.58	31.26
1450	0.82	29.92	30.90
1500	0.86	29.45	29.24
1550	0.88	29.42	28.86
1600	0.92	29.56	29.55
1650	0.95	29.19	29.85
1700	0.98	29.21	29.62
1750	1.01	29.47	30.65
1850	1.08	29.33	31.06
1900	1.12	29.63	28.73
1950	1.17	29.46	27.42
2000	1.21	29.19	26.09
2100	1.32	28.27	24.00
2200	1.44	26.62	23.68
2300	1.60	24.63	21.08
2350	1.68	23.53	19.84
2400	1.78	22.33	18.52
2500	2.03	20.29	17.60

