

Fixed Attenuator

FW-12+

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
10.0	11.97	1.02
50.0	11.98	1.02
100.0	12.00	1.02
500.0	12.05	1.01
1000.0	12.09	1.01
1200.0	12.10	1.01
1400.0	12.12	1.01
1600.0	12.14	1.01
1800.0	12.15	1.01
2000.0	12.17	1.02
2200.0	12.18	1.02
2400.0	12.21	1.02
2600.0	12.23	1.02
2800.0	12.25	1.03
3000.0	12.27	1.03
3200.0	12.28	1.03
3400.0	12.31	1.03
3600.0	12.33	1.03
3800.0	12.35	1.03
4000.0	12.37	1.03
4200.0	12.39	1.03
4400.0	12.41	1.04
4600.0	12.44	1.03
4800.0	12.46	1.03
5000.0	12.48	1.03
5200.0	12.50	1.03
5500.0	12.54	1.03
6000.0	12.60	1.04
6500.0	12.66	1.06
7000.0	12.73	1.10
7500.0	12.79	1.15
8000.0	12.82	1.19
8500.0	12.87	1.24
9000.0	12.91	1.29
9500.0	12.97	1.34
10000.0	13.00	1.37
10500.0	13.02	1.38
11000.0	13.03	1.37
11500.0	13.03	1.35
12000.0	13.02	1.33
12500.0	13.02	1.31
13000.0	12.97	1.30
13500.0	12.94	1.27
14000.0	12.92	1.26
14500.0	12.84	1.23
15000.0	12.84	1.19



P.O. Box 350166, Brooklyn, New York 11235-0003 • (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS



REV. OR
FW-12+
5/1/2014
Page 1 of 1