

Coaxial Fixed Attenuator

FW-20A+

Typical Performance Data

| FREQ. | ATTENUATION | VSWR |
|-------|-------------|------|
| (MHz) | (dB) | (:1) |
| 10 | 20.02 | 1.13 |
| 20 | 20.02 | 1.13 |
| 50 | 20.03 | 1.13 |
| 100 | 20.03 | 1.13 |
| 200 | 20.05 | 1.13 |
| 300 | 20.06 | 1.13 |
| 400 | 20.07 | 1.13 |
| 500 | 20.08 | 1.13 |
| 600 | 20.10 | 1.13 |
| 700 | 20.11 | 1.13 |
| 800 | 20.12 | 1.13 |
| 900 | 20.13 | 1.13 |
| 1000 | 20.14 | 1.13 |
| 1200 | 20.16 | 1.13 |
| 1400 | 20.19 | 1.13 |
| 1600 | 20.21 | 1.13 |
| 1800 | 20.23 | 1.13 |
| 2000 | 20.25 | 1.13 |
| 2200 | 20.28 | 1.13 |
| 2400 | 20.30 | 1.13 |
| 2600 | 20.33 | 1.13 |
| 2800 | 20.36 | 1.13 |
| 3000 | 20.38 | 1.12 |
| 3200 | 20.42 | 1.12 |
| 3400 | 20.45 | 1.12 |
| 3600 | 20.48 | 1.11 |
| 3800 | 20.51 | 1.11 |
| 4000 | 20.54 | 1.11 |
| 4200 | 20.58 | 1.11 |
| 4400 | 20.61 | 1.10 |
| 4600 | 20.65 | 1.10 |
| 4800 | 20.69 | 1.10 |
| 5000 | 20.73 | 1.10 |
| 5200 | 20.77 | 1.10 |
| 5400 | 20.81 | 1.10 |
| 5600 | 20.85 | 1.10 |
| 5800 | 20.89 | 1.10 |
| 6000 | 20.92 | 1.10 |
| 6200 | 20.96 | 1.10 |
| 6400 | 21.00 | 1.09 |
| 6600 | 21.05 | 1.09 |
| 6800 | 21.09 | 1.09 |
| 7000 | 21.13 | 1.09 |
| 7200 | 21.18 | 1.08 |
| 7400 | 21.21 | 1.08 |
| 7600 | 21.25 | 1.07 |
| 7800 | 21.29 | 1.06 |
| 8000 | 21.33 | 1.06 |
| 8200 | 21.36 | 1.05 |
| 8400 | 21.40 | 1.04 |
| 8600 | 21.43 | 1.04 |
| 8800 | 21.46 | 1.04 |
| 9000 | 21.49 | 1.04 |
| 9200 | 21.52 | 1.04 |
| 9400 | 21.55 | 1.05 |
| 9600 | 21.57 | 1.05 |
| 10000 | 21.61 | 1.07 |
| 11000 | 21.67 | 1.11 |
| 11500 | 21.68 | 1.12 |
| 12000 | 21.67 | 1.14 |



ISO 9001 ISO 14001 AS 9100 CERTIFIED



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS