

Coaxial Fixed Attenuator

FW-5A+

Typical Performance Data

| FREQ. | ATTENUATION | VSWR |
|-------|-------------|------|
| (MHz) | (dB) | (:1) |
| 10 | 4.91 | 1.07 |
| 20 | 4.91 | 1.07 |
| 50 | 4.91 | 1.07 |
| 100 | 4.92 | 1.07 |
| 200 | 4.93 | 1.07 |
| 300 | 4.94 | 1.07 |
| 400 | 4.95 | 1.07 |
| 500 | 4.96 | 1.07 |
| 600 | 4.97 | 1.07 |
| 700 | 4.98 | 1.07 |
| 800 | 4.99 | 1.07 |
| 900 | 4.99 | 1.07 |
| 1000 | 5.01 | 1.07 |
| 1200 | 5.02 | 1.06 |
| 1400 | 5.03 | 1.06 |
| 1600 | 5.04 | 1.06 |
| 1800 | 5.06 | 1.06 |
| 2000 | 5.07 | 1.06 |
| 2200 | 5.08 | 1.06 |
| 2400 | 5.09 | 1.06 |
| 2600 | 5.10 | 1.05 |
| 2800 | 5.11 | 1.05 |
| 3000 | 5.12 | 1.05 |
| 3200 | 5.13 | 1.05 |
| 3400 | 5.13 | 1.05 |
| 3600 | 5.14 | 1.05 |
| 3800 | 5.15 | 1.05 |
| 4000 | 5.16 | 1.05 |
| 4200 | 5.17 | 1.05 |
| 4400 | 5.17 | 1.05 |
| 4600 | 5.18 | 1.05 |
| 4800 | 5.19 | 1.05 |
| 5000 | 5.20 | 1.06 |
| 5200 | 5.21 | 1.06 |
| 5400 | 5.22 | 1.07 |
| 5600 | 5.23 | 1.07 |
| 5800 | 5.24 | 1.07 |
| 6000 | 5.24 | 1.07 |
| 6200 | 5.25 | 1.07 |
| 6400 | 5.26 | 1.07 |
| 6600 | 5.27 | 1.07 |
| 6800 | 5.28 | 1.06 |
| 7000 | 5.29 | 1.06 |
| 7200 | 5.30 | 1.05 |
| 7400 | 5.31 | 1.05 |
| 7600 | 5.32 | 1.04 |
| 7800 | 5.33 | 1.04 |
| 8000 | 5.34 | 1.04 |
| 8200 | 5.35 | 1.04 |
| 8400 | 5.36 | 1.04 |
| 8600 | 5.36 | 1.05 |
| 8800 | 5.37 | 1.06 |
| 9000 | 5.38 | 1.07 |
| 9200 | 5.39 | 1.08 |
| 9400 | 5.40 | 1.09 |
| 9600 | 5.41 | 1.10 |
| 10000 | 5.43 | 1.11 |
| 11000 | 5.45 | 1.12 |
| 11500 | 5.47 | 1.12 |
| 12000 | 5.48 | 1.13 |



ISO 9001 ISO 14001 AS 9100 CERTIFIED

