

# Coaxial Fixed Attenuator

FW-6A+

## Typical Performance Data

| FREQ. | ATTENUATION | VSWR |
|-------|-------------|------|
| (MHz) | (dB)        | (:1) |
| 10    | 5.95        | 1.03 |
| 20    | 5.95        | 1.03 |
| 50    | 5.96        | 1.03 |
| 100   | 5.96        | 1.03 |
| 200   | 5.98        | 1.03 |
| 300   | 5.99        | 1.03 |
| 400   | 6.00        | 1.03 |
| 500   | 6.01        | 1.03 |
| 600   | 6.01        | 1.03 |
| 700   | 6.02        | 1.03 |
| 800   | 6.03        | 1.03 |
| 900   | 6.04        | 1.03 |
| 1000  | 6.05        | 1.03 |
| 1200  | 6.06        | 1.03 |
| 1400  | 6.07        | 1.04 |
| 1600  | 6.09        | 1.04 |
| 1800  | 6.10        | 1.04 |
| 2000  | 6.11        | 1.04 |
| 2200  | 6.12        | 1.05 |
| 2400  | 6.13        | 1.05 |
| 2600  | 6.15        | 1.05 |
| 2800  | 6.16        | 1.05 |
| 3000  | 6.17        | 1.06 |
| 3200  | 6.18        | 1.06 |
| 3400  | 6.19        | 1.06 |
| 3600  | 6.20        | 1.06 |
| 3800  | 6.21        | 1.06 |
| 4000  | 6.22        | 1.05 |
| 4200  | 6.23        | 1.05 |
| 4400  | 6.24        | 1.05 |
| 4600  | 6.25        | 1.04 |
| 4800  | 6.26        | 1.04 |
| 5000  | 6.27        | 1.04 |
| 5200  | 6.28        | 1.04 |
| 5400  | 6.29        | 1.04 |
| 5600  | 6.30        | 1.04 |
| 5800  | 6.31        | 1.04 |
| 6000  | 6.32        | 1.04 |
| 6200  | 6.33        | 1.04 |
| 6400  | 6.35        | 1.04 |
| 6600  | 6.36        | 1.04 |
| 6800  | 6.37        | 1.05 |
| 7000  | 6.38        | 1.05 |
| 7200  | 6.39        | 1.05 |
| 7400  | 6.40        | 1.05 |
| 7600  | 6.41        | 1.05 |
| 7800  | 6.42        | 1.05 |
| 8000  | 6.43        | 1.05 |
| 8200  | 6.44        | 1.05 |
| 8400  | 6.45        | 1.05 |
| 8600  | 6.46        | 1.04 |
| 8800  | 6.47        | 1.04 |
| 9000  | 6.48        | 1.03 |
| 9200  | 6.49        | 1.03 |
| 9400  | 6.49        | 1.02 |
| 9600  | 6.50        | 1.02 |
| 10000 | 6.52        | 1.03 |
| 11000 | 6.55        | 1.08 |
| 11500 | 6.57        | 1.11 |
| 12000 | 6.60        | 1.15 |