

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
10.0	7.01	1.02
50.0	7.04	1.02
100.0	7.05	1.02
500.0	7.11	1.01
1000.0	7.14	1.01
1200.0	7.15	1.01
1400.0	7.17	1.02
1600.0	7.18	1.02
1800.0	7.19	1.02
2000.0	7.21	1.02
2200.0	7.22	1.03
2400.0	7.23	1.03
2600.0	7.25	1.04
2800.0	7.26	1.04
3000.0	7.27	1.05
3200.0	7.28	1.06
3400.0	7.30	1.06
3600.0	7.32	1.07
3800.0	7.33	1.08
4000.0	7.34	1.08
4200.0	7.36	1.09
4400.0	7.37	1.09
4600.0	7.38	1.09
4800.0	7.40	1.10
5000.0	7.41	1.10
5200.0	7.43	1.10
5500.0	7.44	1.10
6000.0	7.47	1.10
6500.0	7.50	1.10
7000.0	7.54	1.11
7500.0	7.57	1.11
8000.0	7.59	1.12
8500.0	7.63	1.13
9000.0	7.67	1.13
9500.0	7.70	1.15
10000.0	7.70	1.16
10500.0	7.71	1.16
11000.0	7.75	1.16
11500.0	7.75	1.16
12000.0	7.73	1.17
12500.0	7.73	1.19
13000.0	7.71	1.19
13500.0	7.71	1.18
14000.0	7.71	1.17
14500.0	7.67	1.15
15000.0	7.69	1.12