

Coaxial Fixed Attenuator

FW-8A+

Typical Performance Data

| FREQ. | ATTENUATION | VSWR |
|-------|-------------|------|
| (MHz) | (dB) | (:1) |
| 10 | 7.99 | 1.13 |
| 20 | 7.99 | 1.13 |
| 50 | 8.00 | 1.13 |
| 100 | 8.00 | 1.13 |
| 200 | 8.02 | 1.12 |
| 300 | 8.03 | 1.12 |
| 400 | 8.04 | 1.12 |
| 500 | 8.05 | 1.12 |
| 600 | 8.05 | 1.12 |
| 700 | 8.06 | 1.12 |
| 800 | 8.07 | 1.13 |
| 900 | 8.08 | 1.13 |
| 1000 | 8.09 | 1.13 |
| 1200 | 8.10 | 1.13 |
| 1400 | 8.12 | 1.13 |
| 1600 | 8.13 | 1.13 |
| 1800 | 8.15 | 1.13 |
| 2000 | 8.16 | 1.13 |
| 2200 | 8.17 | 1.13 |
| 2400 | 8.19 | 1.13 |
| 2600 | 8.20 | 1.13 |
| 2800 | 8.21 | 1.12 |
| 3000 | 8.22 | 1.12 |
| 3200 | 8.23 | 1.12 |
| 3400 | 8.24 | 1.11 |
| 3600 | 8.25 | 1.11 |
| 3800 | 8.26 | 1.10 |
| 4000 | 8.27 | 1.10 |
| 4200 | 8.28 | 1.10 |
| 4400 | 8.29 | 1.09 |
| 4600 | 8.30 | 1.09 |
| 4800 | 8.31 | 1.09 |
| 5000 | 8.32 | 1.09 |
| 5200 | 8.34 | 1.09 |
| 5400 | 8.35 | 1.09 |
| 5600 | 8.36 | 1.09 |
| 5800 | 8.38 | 1.09 |
| 6000 | 8.39 | 1.09 |
| 6200 | 8.40 | 1.09 |
| 6400 | 8.42 | 1.09 |
| 6600 | 8.43 | 1.09 |
| 6800 | 8.44 | 1.09 |
| 7000 | 8.46 | 1.08 |
| 7200 | 8.47 | 1.08 |
| 7400 | 8.48 | 1.07 |
| 7600 | 8.49 | 1.06 |
| 7800 | 8.51 | 1.06 |
| 8000 | 8.52 | 1.05 |
| 8200 | 8.53 | 1.04 |
| 8400 | 8.54 | 1.04 |
| 8600 | 8.55 | 1.04 |
| 8800 | 8.56 | 1.04 |
| 9000 | 8.57 | 1.05 |
| 9200 | 8.58 | 1.06 |
| 9400 | 8.59 | 1.07 |
| 9600 | 8.60 | 1.08 |
| 10000 | 8.62 | 1.11 |
| 11000 | 8.65 | 1.16 |
| 11500 | 8.65 | 1.16 |
| 12000 | 8.66 | 1.17 |



ISO 9001 ISO 14001 AS 9100 CERTIFIED

