

Typical Performance Data

FREQ.	ATTENUATION	VSWR
(MHz)	(dB)	(:1)
10	11.98	1.14
20	11.99	1.14
50	12.00	1.14
80	12.01	1.13
100	12.01	1.13
120	12.01	1.13
150	12.03	1.13
180	12.03	1.13
210	12.04	1.14
240	12.04	1.14
270	12.05	1.14
300	12.06	1.14
330	12.06	1.14
360	12.07	1.14
390	12.07	1.15
420	12.07	1.15
450	12.08	1.15
480	12.08	1.15
500	12.09	1.15
530	12.09	1.16
560	12.10	1.16
590	12.10	1.16
620	12.11	1.16
650	12.11	1.16
680	12.12	1.17
710	12.12	1.17
750	12.13	1.17
780	12.13	1.17
810	12.14	1.18
840	12.14	1.18
890	12.14	1.18
920	12.15	1.18
950	12.15	1.18
980	12.16	1.19
1000	12.16	1.19
1030	12.16	1.19
1050	12.17	1.19
1080	12.17	1.19
1110	12.18	1.19
1150	12.18	1.19
1180	12.19	1.19
1200	12.19	1.19
1230	12.19	1.19
1250	12.19	1.19
1280	12.20	1.19
1300	12.20	1.19
1350	12.21	1.19
1400	12.21	1.19
1450	12.22	1.19
1500	12.22	1.19
1550	12.23	1.19
1600	12.23	1.18
1650	12.24	1.18
1700	12.25	1.18
1750	12.25	1.17
1800	12.26	1.17
1850	12.26	1.17
1900	12.27	1.16
1950	12.27	1.16
2000	12.28	1.15