

Typical Performance Data

FREQ.	ATTENUATION	VSWR
(MHz)	(dB)	(:1)
10	14.96	1.12
20	14.97	1.12
50	14.98	1.12
80	14.99	1.12
100	15.00	1.12
120	15.00	1.12
150	15.01	1.12
180	15.02	1.12
210	15.02	1.12
240	15.02	1.13
270	15.03	1.13
300	15.04	1.13
330	15.04	1.13
360	15.05	1.13
390	15.05	1.13
420	15.05	1.14
450	15.06	1.14
480	15.06	1.14
500	15.07	1.14
530	15.07	1.15
560	15.08	1.15
590	15.09	1.15
620	15.09	1.15
650	15.09	1.16
680	15.10	1.16
710	15.10	1.16
750	15.11	1.16
780	15.12	1.17
810	15.12	1.17
840	15.12	1.17
890	15.13	1.17
920	15.13	1.18
950	15.14	1.18
980	15.14	1.18
1000	15.14	1.18
1030	15.15	1.18
1050	15.15	1.18
1080	15.16	1.18
1110	15.16	1.19
1150	15.17	1.19
1180	15.17	1.19
1200	15.17	1.19
1230	15.18	1.19
1250	15.18	1.19
1280	15.19	1.19
1300	15.19	1.19
1350	15.20	1.19
1400	15.20	1.19
1450	15.21	1.19
1500	15.22	1.19
1550	15.22	1.19
1600	15.23	1.18
1650	15.23	1.18
1700	15.24	1.18
1750	15.25	1.17
1800	15.25	1.17
1850	15.26	1.17
1900	15.26	1.16
1950	15.27	1.16
2000	15.28	1.16