

Typical Performance Data

FREQ.	ATTENUATION	VSWR
(MHz)	(dB)	(:1)
10	20.04	1.16
20	20.04	1.16
50	20.05	1.16
80	20.07	1.16
100	20.07	1.16
120	20.07	1.16
150	20.08	1.16
180	20.08	1.16
210	20.09	1.16
240	20.10	1.16
270	20.10	1.16
300	20.11	1.16
330	20.11	1.16
360	20.12	1.17
390	20.12	1.17
420	20.13	1.17
450	20.13	1.17
480	20.14	1.17
500	20.14	1.17
530	20.14	1.18
560	20.15	1.18
590	20.16	1.18
620	20.16	1.18
650	20.17	1.18
680	20.17	1.19
710	20.17	1.19
750	20.18	1.19
780	20.19	1.19
810	20.20	1.19
840	20.20	1.19
890	20.20	1.20
920	20.21	1.20
950	20.22	1.20
980	20.22	1.20
1000	20.22	1.20
1030	20.23	1.20
1050	20.23	1.20
1080	20.24	1.20
1110	20.24	1.20
1150	20.25	1.20
1180	20.25	1.20
1200	20.26	1.20
1230	20.26	1.20
1250	20.27	1.20
1280	20.27	1.20
1300	20.28	1.20
1350	20.28	1.20
1400	20.29	1.20
1450	20.30	1.19
1500	20.31	1.19
1550	20.32	1.19
1600	20.32	1.18
1650	20.33	1.18
1700	20.33	1.17
1750	20.34	1.17
1800	20.35	1.16
1850	20.36	1.16
1900	20.37	1.15
1950	20.37	1.15
2000	20.39	1.14