

*Typical Performance Data*

| FREQ. | ATTENUATION | VSWR |
|-------|-------------|------|
| (MHz) | (dB)        | (:1) |
| 10    | 1.96        | 1.07 |
| 20    | 1.96        | 1.07 |
| 50    | 1.97        | 1.07 |
| 80    | 1.98        | 1.07 |
| 100   | 1.99        | 1.07 |
| 120   | 1.99        | 1.07 |
| 150   | 1.99        | 1.07 |
| 180   | 2.00        | 1.07 |
| 210   | 2.01        | 1.07 |
| 240   | 2.01        | 1.07 |
| 270   | 2.01        | 1.07 |
| 300   | 2.02        | 1.07 |
| 330   | 2.02        | 1.07 |
| 360   | 2.03        | 1.07 |
| 390   | 2.03        | 1.07 |
| 420   | 2.03        | 1.07 |
| 450   | 2.04        | 1.07 |
| 480   | 2.04        | 1.07 |
| 500   | 2.04        | 1.07 |
| 530   | 2.05        | 1.07 |
| 560   | 2.05        | 1.07 |
| 590   | 2.06        | 1.08 |
| 620   | 2.06        | 1.08 |
| 650   | 2.06        | 1.08 |
| 680   | 2.07        | 1.08 |
| 710   | 2.07        | 1.08 |
| 750   | 2.07        | 1.08 |
| 780   | 2.08        | 1.08 |
| 810   | 2.08        | 1.09 |
| 840   | 2.08        | 1.09 |
| 890   | 2.09        | 1.09 |
| 920   | 2.09        | 1.09 |
| 950   | 2.10        | 1.10 |
| 980   | 2.10        | 1.10 |
| 1000  | 2.10        | 1.10 |
| 1030  | 2.11        | 1.11 |
| 1050  | 2.11        | 1.11 |
| 1080  | 2.11        | 1.11 |
| 1110  | 2.12        | 1.12 |
| 1150  | 2.12        | 1.12 |
| 1180  | 2.13        | 1.12 |
| 1200  | 2.13        | 1.13 |
| 1230  | 2.13        | 1.13 |
| 1250  | 2.13        | 1.13 |
| 1280  | 2.13        | 1.14 |
| 1300  | 2.14        | 1.14 |
| 1350  | 2.14        | 1.15 |
| 1400  | 2.15        | 1.15 |
| 1450  | 2.15        | 1.16 |
| 1500  | 2.16        | 1.17 |
| 1550  | 2.16        | 1.17 |
| 1600  | 2.17        | 1.18 |
| 1650  | 2.17        | 1.18 |
| 1700  | 2.17        | 1.18 |
| 1750  | 2.18        | 1.19 |
| 1800  | 2.18        | 1.19 |
| 1850  | 2.19        | 1.19 |
| 1900  | 2.19        | 1.19 |
| 1950  | 2.19        | 1.19 |
| 2000  | 2.19        | 1.19 |