

Ceramic High Pass Filter

HFCN-1910-4+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
1	84.52	90.73	82.00	0.00	0.01	0.01	0.00	0.01	0.01
50	69.41	75.59	66.98	0.00	0.01	0.01	0.00	0.01	0.01
100	69.54	87.69	74.07	0.01	0.01	0.00	0.01	0.02	0.01
290	67.18	62.97	68.59	0.01	0.03	0.08	0.02	0.04	0.05
500	62.69	63.78	62.84	0.03	0.07	0.11	0.02	0.05	0.08
855	74.58	84.86	90.06	0.07	0.16	0.21	0.09	0.17	0.20
900	70.27	68.45	66.73	0.11	0.19	0.25	0.10	0.15	0.19
945	61.35	60.27	59.66	0.11	0.19	0.25	0.12	0.19	0.21
1040	50.85	50.40	49.72	0.16	0.24	0.30	0.14	0.22	0.26
1075	47.92	47.37	46.90	0.19	0.27	0.33	0.16	0.22	0.27
1100	45.90	45.42	44.98	0.18	0.27	0.32	0.18	0.25	0.31
1170	40.57	40.21	39.73	0.21	0.29	0.37	0.21	0.28	0.34
1325	30.40	29.98	29.48	0.32	0.41	0.51	0.30	0.40	0.46
1400	25.77	25.38	24.87	0.36	0.50	0.58	0.39	0.49	0.58
1490	20.44	19.98	19.54	0.49	0.63	0.76	0.53	0.65	0.78
1665	10.20	9.89	9.51	1.26	1.54	1.83	1.37	1.64	1.93
1775	4.99	4.80	4.63	3.20	3.71	4.30	3.43	4.00	4.65
1840	2.90	2.89	2.83	5.50	6.28	7.12	5.91	6.79	7.77
1910	1.64	1.73	1.79	9.11	10.16	11.23	9.78	11.05	12.42
1950	1.27	1.40	1.48	11.44	12.59	13.72	12.40	13.88	15.50
2000	0.99	1.13	1.24	14.42	15.54	16.79	15.73	17.36	19.11
2050	0.81	0.97	1.09	17.13	18.06	19.24	18.74	20.10	21.70
2100	0.71	0.87	1.02	19.28	19.89	21.03	20.83	21.46	22.57
2150	0.65	0.81	0.93	20.46	20.77	21.96	21.95	22.02	22.88
2200	0.60	0.75	0.89	21.47	21.69	23.05	22.40	22.25	23.00
2400	0.49	0.66	0.77	22.54	23.13	23.98	22.27	22.49	22.95
2700	0.40	0.55	0.69	20.94	21.20	21.65	20.61	20.65	20.71
3500	0.32	0.48	0.62	25.00	25.68	28.34	25.17	24.92	26.44
4000	0.30	0.49	0.64	22.10	22.36	21.76	21.81	21.60	20.22
4400	0.45	0.67	0.84	15.77	15.15	14.60	15.63	14.97	14.32
4450	0.52	0.73	0.95	15.46	14.54	14.14	15.40	14.43	14.11
4500	0.53	0.76	0.94	14.35	13.81	13.20	14.29	13.73	13.01
5000	0.86	1.13	1.28	9.70	9.64	9.65	9.69	9.48	9.34
5200	1.07	1.37	1.48	8.64	8.58	8.73	8.67	8.38	8.39
6000	2.34	2.70	2.99	5.09	5.31	5.24	4.91	4.96	4.79
7000	4.15	4.34	4.75	3.18	3.23	3.26	2.85	3.07	3.24
8000	6.17	6.06	6.39	2.17	2.44	2.74	2.10	2.37	2.67
9000	6.56	7.10	7.58	1.68	1.84	1.97	1.74	1.88	1.90
10000	7.74	7.97	8.24	1.28	1.56	1.79	1.33	1.55	1.68
11000	13.56	13.51	14.14	2.01	1.72	1.80	0.94	1.19	1.40
12000	10.79	8.83	7.54	1.52	2.67	4.08	1.75	2.47	3.40
13000	1.74	2.15	3.25	8.91	10.55	11.70	7.59	8.70	8.24



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR
HFCN-1910-4+
080723
Page 1 of 1