

Switch SPST , 50W

KSWHA-1-20+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS C1=-8V,C2=0V (dB) IN-OUT , "ON"	ISOLATION C1=0V,C2=-8V (dB) IN-OUT , "OFF"	VSWR		
			IN	(:1) OUT , "ON"	OUT , "OFF"
0	0.62	90.61	1.15	1.15	1.03
5	0.63	85.48	1.16	1.15	1.03
10	0.69	83.23	1.16	1.15	1.03
100	0.79	67.92	1.15	1.15	1.03
280	0.85	66.96	1.15	1.14	1.03
390	0.92	67.09	1.15	1.14	1.03
445	0.90	67.05	1.16	1.15	1.03
610	0.96	65.89	1.16	1.15	1.04
780	0.99	64.48	1.17	1.16	1.05
890	1.02	63.58	1.18	1.16	1.06
945	1.04	63.07	1.18	1.16	1.07
1000	0.99	62.55	1.18	1.15	1.08
1165	1.09	61.49	1.18	1.15	1.09
1335	1.11	61.45	1.17	1.14	1.12
1445	1.14	61.66	1.16	1.13	1.13
1500	1.09	62.32	1.16	1.12	1.14
1665	1.17	60.72	1.15	1.10	1.17
1835	1.13	60.34	1.14	1.07	1.20
1945	1.22	60.54	1.13	1.06	1.22
2000	1.17	61.08	1.13	1.05	1.23