

Ceramic Low Pass Filter

LFCN-3400D+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
40	0.03	0.03	0.04	53.18	42.74	37.82	48.23	40.56	36.60
100	0.00	0.02	0.03	46.05	47.47	37.74	44.61	45.67	37.82
500	0.04	0.08	0.10	36.62	33.82	28.67	35.66	33.17	28.32
1000	0.09	0.14	0.18	26.11	26.27	25.24	25.89	26.08	25.01
1500	0.14	0.22	0.25	22.05	21.81	22.73	21.89	21.68	22.66
2000	0.20	0.30	0.33	18.36	18.07	18.69	18.33	18.04	18.59
2500	0.32	0.42	0.49	15.10	15.14	15.13	15.01	15.12	15.05
3000	0.48	0.62	0.72	12.68	12.59	12.46	12.75	12.66	12.53
3200	0.58	0.73	0.84	11.68	11.64	11.59	11.72	11.73	11.73
3400	0.74	0.90	1.07	10.77	10.86	10.71	10.73	10.86	10.98
3500	0.84	1.02	1.22	10.37	10.50	10.31	10.30	10.43	10.60
3600	0.95	1.13	1.35	10.03	10.22	10.18	9.87	10.02	10.16
3675	1.07	1.27	1.47	9.83	10.10	10.24	9.50	9.66	9.72
3800	1.37	1.62	1.84	9.61	9.96	10.24	8.71	8.83	8.76
3900	1.86	2.22	2.56	9.27	9.53	9.80	7.57	7.56	7.34
3950	2.33	2.80	3.26	8.67	8.80	8.93	6.64	6.54	6.24
4000	3.08	3.73	4.39	7.58	7.58	7.49	5.48	5.34	4.98
4110	6.90	8.21	9.59	4.38	4.31	4.18	2.78	2.77	2.58
4200	13.61	15.76	17.94	2.45	2.54	2.60	1.51	1.69	1.66
4300	27.96	29.03	28.35	1.48	1.69	1.83	1.05	1.28	1.33
4330	29.85	27.78	26.41	1.38	1.58	1.74	1.07	1.29	1.35
4400	24.26	23.67	23.32	1.14	1.36	1.52	0.99	1.20	1.28
4600	24.41	25.37	25.99	0.70	0.90	1.07	0.80	1.03	1.11
4800	35.82	34.96	32.67	0.60	0.77	0.95	0.70	0.98	1.04
5000	24.99	24.24	23.53	0.47	0.65	0.80	0.66	0.92	1.04
5500	18.69	18.86	18.96	0.40	0.55	0.64	0.55	0.86	0.92
6000	19.58	20.10	20.25	0.36	0.50	0.58	0.55	0.78	0.98
6500	22.92	23.45	23.66	0.39	0.54	0.66	0.65	0.56	0.62
7000	28.92	29.04	28.02	0.42	0.62	0.79	0.61	0.66	0.83
7400	30.50	30.55	30.04	0.46	0.68	0.95	0.59	0.68	0.74
7800	27.13	26.35	27.15	0.54	0.79	1.04	0.49	0.68	0.74
8000	24.21	23.76	24.90	0.61	0.88	1.12	0.56	0.72	0.75
8300	21.21	20.92	20.91	0.72	0.96	1.23	0.56	0.75	0.81
9000	10.32	9.99	9.52	1.56	1.92	2.31	1.34	1.84	2.40
9250	4.48	4.44	4.58	5.65	7.15	8.24	6.34	8.90	11.72
9500	5.07	6.40	7.40	4.86	3.96	3.57	4.53	3.71	3.42
10000	12.50	13.35	14.33	1.26	1.42	1.56	0.89	1.14	1.29
11000	16.14	15.82	16.10	0.97	1.27	1.40	0.85	1.16	1.38
12000	11.85	12.06	12.17	1.18	1.46	1.76	1.21	1.32	1.55
14000	7.38	7.30	7.30	2.93	3.63	4.59	1.88	2.30	2.72
15000	12.91	14.57	14.97	2.98	3.43	3.82	1.67	1.96	2.23
16000	17.41	17.72	17.12	3.22	3.21	3.14	1.43	2.21	2.71
18000	15.11	15.28	16.77	3.5	3.920	4.0	2.26	2.49	2.37
20000	8.10	8.02	7.90	2.0	2.570	3.1	3.63	4.63	5.71

REV. X1

LFCN-3400D+

080131

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

