

# Ceramic Low Pass Filter

# LFCN-6700D+

## Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	0.03	0.05	0.05	40.67	38.15	36.52	40.25	37.82	36.50
100	0.05	0.06	0.07	40.35	37.59	35.75	40.34	37.70	35.81
200	0.05	0.07	0.09	34.69	34.93	34.68	34.98	35.33	35.22
500	0.08	0.11	0.13	29.02	29.48	30.54	29.50	30.23	31.40
1000	0.10	0.16	0.20	25.77	26.14	27.33	26.40	26.86	28.16
2000	0.13	0.21	0.29	30.68	31.75	31.60	32.08	33.95	34.37
3000	0.18	0.30	0.40	26.59	25.88	25.10	26.99	26.29	25.52
4000	0.21	0.37	0.51	21.49	21.13	21.14	21.41	21.01	20.95
5000	0.28	0.46	0.64	18.90	18.81	18.28	18.66	18.67	18.36
6000	0.48	0.69	0.91	16.11	16.21	16.24	16.81	16.84	16.88
6350	0.62	0.85	1.08	14.81	14.77	14.75	16.37	16.33	16.44
6700	0.85	1.12	1.38	13.21	13.02	12.80	16.31	16.24	16.22
7200	1.43	1.76	2.08	9.89	9.68	9.40	13.56	13.35	13.41
7600	2.53	2.98	3.39	6.27	6.20	6.06	8.42	8.17	8.07
7900	4.26	4.94	5.54	3.66	3.62	3.54	4.95	4.79	4.49
8100	6.09	6.93	7.71	2.37	2.45	2.54	3.09	3.02	2.88
8350	9.15	10.23	11.23	1.40	1.59	1.81	1.68	1.71	1.70
8500	11.49	12.64	13.68	1.05	1.31	1.59	1.17	1.28	1.33
8660	14.09	15.36	16.48	0.87	1.14	1.44	0.84	1.00	1.11
8900	18.37	19.73	20.99	0.77	1.09	1.41	0.55	0.78	0.96
8950	19.32	20.68	21.92	0.72	1.04	1.36	0.50	0.74	0.95
9200	24.08	25.54	27.01	0.71	1.01	1.31	0.39	0.66	0.89
9300	25.96	27.44	29.04	0.76	1.05	1.35	0.38	0.66	0.92
9350	26.73	28.31	29.86	0.79	1.06	1.36	0.38	0.65	0.92
9500	29.33	30.25	31.29	0.76	1.08	1.39	0.37	0.66	0.98
9650	30.66	31.27	32.06	0.82	1.07	1.36	0.34	0.66	1.01
10100	29.57	29.74	29.10	0.93	1.17	1.45	0.45	0.77	1.16
11000	23.79	24.28	23.61	0.92	1.27	1.54	0.68	0.94	1.29
11660	21.34	21.12	20.83	0.90	1.18	1.46	0.75	1.09	1.41
12000	19.75	20.06	19.85	1.00	1.27	1.55	0.97	1.20	1.49
12800	17.97	18.51	18.56	1.27	1.35	1.50	1.23	1.58	1.69
13900	16.59	16.66	17.18	1.10	1.51	1.77	1.66	2.13	2.36
14900	17.91	18.01	18.16	0.99	1.54	2.10	2.01	2.30	2.56
15700	18.05	18.08	18.57	1.38	1.79	2.33	1.93	2.32	2.87
16300	18.42	18.67	19.08	1.60	1.96	2.57	2.16	2.32	2.81
16500	18.48	18.64	19.32	1.77	2.14	2.75	1.88	2.26	2.73
17000	18.76	19.13	19.25	3.87	5.96	7.32	2.02	2.18	2.49
18000	19.30	20.01	20.26	2.48	2.70	3.05	1.41	1.77	2.21
18560	21.02	21.99	22.82	1.95	2.21	2.36	1.13	1.49	1.95
19000	23.61	24.75	25.29	1.52	1.58	1.72	1.00	1.36	1.81
19200	25.20	26.32	26.84	1.30	1.55	1.73	0.72	1.19	1.77
20000	26.83	26.15	25.64	0.67	1.21	1.72	0.40	0.80	1.35

REV. X1  
LFCN-6700D+  
080722  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

