

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	VSWR (:1)
5	0.07	1.00
10	0.08	1.01
20	0.10	1.02
30	0.12	1.04
40	0.13	1.05
50	0.14	1.06
60	0.15	1.07
70	0.15	1.09
80	0.16	1.10
90	0.17	1.12
100	0.18	1.13
150	0.21	1.19
200	0.26	1.26
250	0.31	1.31
300	0.35	1.34
350	0.38	1.36
400	0.41	1.35
450	0.43	1.32
500	0.45	1.27
550	0.47	1.19
600	0.52	1.11
650	0.59	1.04
700	0.72	1.04
750	0.95	1.15
800	1.51	1.52
855	2.87	1.60
900	15.90	6.82
990	52.31	28.76
1000	50.43	30.81
1100	40.34	46.34
1200	53.90	56.49
1300	43.63	62.71
1400	38.42	65.75
1500	37.05	67.83
1600	37.43	69.14
1700	39.36	69.48
1800	42.99	69.04
1900	45.52	68.63
1950	43.28	68.97
2000	40.37	68.59
2100	35.56	67.49
2150	33.69	67.70
2200	32.04	67.54
2300	29.38	65.29
2400	27.19	63.67
2500	25.35	61.50
2600	23.71	58.20
2700	22.28	55.40
2800	20.94	51.88
2900	19.70	47.91
3000	18.53	45.39
3100	17.48	40.52
3200	16.46	37.09
3300	15.47	34.01
3400	14.46	29.88
3500	13.54	26.17