

Ceramic Low Pass Filter

LFTC-1350+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS @ +25° C (dB)	INPUT RETURN LOSS @ +25° C (dB)	OUTPUT RETURNLOSS @ +25° C (dB)
1	0.06	46.06	46.06
50	0.14	30.97	31.19
100	0.18	29.22	29.47
500	0.35	35.35	37.86
1000	0.64	21.87	21.67
1350	0.93	29.03	38.57
1380	0.99	24.68	27.12
1550	2.95	6.19	6.03
1610	4.87	3.61	3.47
1730	9.96	1.48	1.36
1845	14.90	0.83	0.76
1975	19.96	0.57	0.52
2100	24.40	0.48	0.42
2120	25.08	0.48	0.42
2270	30.06	0.43	0.36
2420	35.00	0.40	0.32
2565	40.16	0.40	0.30
2700	45.93	0.41	0.30
2780	50.41	0.38	0.29
2895	60.98	0.37	0.28
2955	67.97	0.38	0.29
3050	57.95	0.35	0.28
3200	52.23	0.35	0.30
3400	49.63	0.35	0.28
4000	48.04	0.41	0.29
4500	43.52	0.41	0.33
4945	39.86	0.44	0.35
5300	36.72	0.50	0.40
6000	31.38	0.63	0.50
6220	29.86	0.78	0.54
6500	25.78	1.64	0.78
6635	21.08	5.11	1.17
6740	16.98	12.72	1.98
6850	14.75	3.20	4.60
7000	16.16	1.53	3.42
7500	23.67	1.02	0.88
7850	11.88	1.97	2.09
8110	8.70	3.62	9.67
8300	14.20	1.77	2.81
8500	21.55	1.19	1.35
9000	23.21	2.72	2.28

REV. X1
LFTC-1350+
071007
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

