

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT VSWR (:1)	OUTPUT VSWR (:1)
500	33.63	351.20	589.33
600	32.88	573.19	534.64
700	32.67	584.98	482.40
800	33.02	1065.18	406.91
900	34.09	683.66	547.07
1000	36.24	467.00	421.04
1100	40.65	248.38	256.90
1200	52.85	175.39	308.31
1300	41.44	127.93	151.76
1400	34.66	104.63	161.11
1500	31.02	83.47	100.87
1600	29.09	66.92	81.30
1700	29.03	52.58	63.06
1800	33.20	40.28	44.57
1900	29.40	27.56	28.99
1917	26.58	25.49	26.60
2000	16.47	15.45	15.36
2100	8.08	6.25	6.08
2200	3.11	2.23	2.10
2300	1.46	1.25	1.09
2400	1.10	1.40	1.39
2405	1.09	1.41	1.40
2410	1.08	1.42	1.41
2415	1.07	1.43	1.42
2420	1.07	1.44	1.43
2425	1.06	1.44	1.44
2430	1.05	1.45	1.45
2435	1.04	1.46	1.46
2440	1.03	1.46	1.47
2445	1.03	1.47	1.47
2450	1.02	1.47	1.48
2455	1.01	1.47	1.49
2460	1.01	1.48	1.49
2465	1.00	1.48	1.50
2470	0.99	1.48	1.50
2475	0.99	1.49	1.50
2480	0.98	1.49	1.51
2485	0.97	1.49	1.51
2490	0.97	1.49	1.51
2495	0.96	1.49	1.52
2500	0.95	1.49	1.52
2550	0.87	1.47	1.51
2600	0.80	1.42	1.48
2650	0.73	1.36	1.43
2700	0.66	1.28	1.37
2750	0.61	1.21	1.31
2800	0.55	1.13	1.26
2850	0.52	1.07	1.23
2900	0.49	1.06	1.22
2950	0.47	1.11	1.24
3000	0.47	1.18	1.29