

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT VSWR (:1)	OUTPUT VSWR (:1)
500	28.43	247.58	1801.42
600	27.02	464.07	478.29
700	25.90	378.89	588.81
800	24.98	2064.52	785.48
900	24.26	1131.02	491.87
1000	23.69	3371.52	540.61
1200	22.98	635.05	418.98
1400	22.81	253.88	520.78
1600	23.20	177.10	345.06
1800	24.34	150.83	243.01
2000	26.76	132.21	208.86
2200	32.49	102.51	134.43
2400	37.06	82.53	96.25
2410	36.28	82.45	93.95
2420	35.20	81.37	92.79
2430	34.50	80.33	91.30
2440	33.54	79.07	90.76
2450	32.92	77.87	90.12
2460	32.04	76.93	88.27
2470	31.48	76.70	87.67
2480	30.68	75.13	85.18
2490	30.18	75.09	83.18
2500	29.47	73.48	80.87
2600	24.63	64.65	68.76
2700	21.03	52.24	55.93
2800	18.09	41.80	42.66
2900	15.53	32.88	34.30
3000	13.24	24.86	25.53
3100	11.14	18.67	19.06
3200	9.22	13.51	13.90
3300	7.45	9.88	10.06
3400	5.88	7.12	7.15
3500	4.50	5.15	5.14
3600	3.36	3.76	3.74
3700	2.46	2.81	2.78
3800	1.79	2.15	2.13
3900	1.33	1.72	1.69
4000	1.03	1.42	1.39
4100	0.85	1.23	1.19
4200	0.74	1.13	1.08
4300	0.68	1.13	1.09
4400	0.64	1.17	1.15
4500	0.61	1.22	1.21
4600	0.58	1.25	1.24
4700	0.56	1.26	1.25
4800	0.53	1.25	1.24
4900	0.51	1.23	1.23
5000	0.48	1.20	1.20
5100	0.46	1.17	1.16
5200	0.43	1.13	1.12
5300	0.42	1.09	1.07
5400	0.40	1.06	1.03
5500	0.40	1.05	1.02
5600	0.39	1.08	1.06
5700	0.39	1.12	1.11
5800	0.40	1.16	1.15
5850	0.40	1.18	1.18
5900	0.41	1.20	1.20
6000	0.41	1.24	1.23
6200	0.43	1.30	1.30
6400	0.45	1.34	1.34
6600	0.46	1.35	1.36
6800	0.46	1.32	1.34
7000	0.44	1.28	1.30
7200	0.43	1.21	1.24
7400	0.43	1.12	1.18
7600	0.43	1.04	1.13
7800	0.45	1.05	1.14
8000	0.49	1.14	1.19