

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	FEMALE RETURN LOSS (dB)	MALE RETURN LOSS (dB)
1000	10.02	14.56	15.38
1050	9.96	15.21	16.33
1250	9.90	16.75	19.08
1400	9.89	17.21	20.08
1500	9.88	17.21	20.44
1650	9.88	16.98	20.44
1750	9.87	16.75	20.44
1900	9.87	16.75	20.08
2000	9.88	16.75	19.73
2150	9.84	16.75	19.40
2400	9.78	16.98	19.08
2500	9.80	17.21	19.08
2600	9.80	17.69	19.08
2750	9.79	18.22	18.78
3000	9.80	20.08	19.08
3100	9.80	20.83	19.40
3500	9.82	27.32	22.12
3600	9.85	30.71	23.13
3750	9.92	46.06	25.66
4000	10.35	24.94	24.29

REV. X1

NAT-10DC-1.5A+

070329

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

