

# Fixed Attenuator, DC Passing

# NAT-15DC-1A+

## Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	FEMALE RETURN LOSS (dB)	MALE RETURN LOSS (dB)
650	15.08	22.12	23.13
700	14.92	24.94	27.32
800	14.90	26.44	30.71
900	15.19	25.66	29.42
1000	14.89	22.61	24.94
1200	14.89	19.73	22.61
1400	14.97	17.95	21.23
1600	15.03	16.75	20.08
1800	15.09	15.94	19.40
2000	15.13	15.38	18.78
2200	15.18	15.04	18.49
2400	15.27	14.88	17.95
2600	15.35	15.04	17.69
2800	15.41	15.56	17.69
3000	15.44	16.13	17.21
3200	15.42	16.98	17.69
3400	15.52	17.95	17.69
3600	15.59	19.08	18.22
3800	15.70	20.08	19.08
4000	15.88	20.83	20.83

REV. X1  
NAT-15DC-1A+  
070329  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

