

Type-N/BNC Adaptenuator

NM-BM-10

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	BNC-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
1	10.01	46.06	46.06
5	10.01	46.06	46.06
10	10.01	46.06	46.06
50	10.02	46.06	46.06
100	10.03	46.06	46.06
500	10.07	46.06	34.15
1000	10.09	40.09	28.30
1500	10.08	34.15	27.32
1700	10.10	30.71	28.30
2000	10.13	27.32	28.30

REV. X1
NM-BM-10
061113
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



Patent Pending The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

