

Plug-In Low Pass Filter (Flat Time Delay)

PBLP-200+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	0.04	35.50	1	1.829
41	0.10	27.00	21	1.915
61	0.16	20.60	41	2.140
81	0.22	16.60	61	2.006
101	0.33	13.40	81	2.109
120	0.52	10.40	101	2.087
121	0.53	10.20	120	2.170
174	2.10	4.70	121	2.113
200	3.22	3.50	148	2.521
201	3.26	3.50	174	2.169
258	6.65	1.60	200	1.964
315	9.45	0.90	201	2.367
344	11.17	0.70	230	1.912
372	13.45	0.50	258	1.485
400	15.58	0.40	287	1.356
401	15.65	0.40	315	2.048
439	17.90	0.30	344	2.142
477	20.36	0.30	372	1.206
496	21.60	0.20	400	0.894
515	22.72	0.20	401	1.205
534	23.75	0.20	420	1.143
535	23.81	0.20	439	0.984
580	26.67	0.20	458	1.412
624	29.26	0.20	477	0.888
668	31.05	0.20	496	0.903
712	33.19	0.30	515	1.244
734	34.36	0.30	534	1.282
756	35.72	0.30	535	0.796
778	37.00	0.30	558	1.491
800	37.94	0.30	580	0.941

REV. X1
PBLP-200+
081222
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

