

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.00	0.21	24.91	1.00	48.070
3.00	0.26	20.32	1.10	47.910
5.00	0.30	20.46	1.30	48.210
7.00	0.33	25.27	1.40	47.670
9.00	0.38	24.09	1.60	48.070
11.00	0.47	20.00	1.80	47.680
13.00	0.58	19.00	2.00	48.300
15.00	0.81	16.36	2.30	48.440
17.00	2.32	7.61	2.50	48.370
19.00	8.82	2.63	2.90	48.630
19.80	12.25	2.04	3.20	48.630
20.60	15.66	1.72	3.60	48.800
21.40	18.93	1.51	4.00	48.880
22.20	22.02	1.36	4.60	49.480
23.00	24.94	1.25	5.10	49.490
23.80	27.72	1.15	5.80	50.430
25.40	32.87	0.99	6.50	50.770
27.10	37.90	0.86	7.30	51.870
28.70	42.24	0.76	8.20	53.050
30.40	46.55	0.67	9.30	54.470
32.00	50.45	0.60	10.40	56.610
33.60	54.18	0.55	11.70	60.330
54.40	77.82	0.22	13.10	66.080
75.20	77.17	0.12	15.00	80.270
96.00	81.80	0.09	17.00	100.530
116.80	80.95	0.08	18.80	81.420
137.60	80.75	0.07	21.10	43.840
158.40	83.26	0.07	23.00	28.310
179.20	79.58	0.06	26.60	15.720
200.00	80.96	0.06	30.00	10.370

REV. X1
PLP-15+
060725

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

